



GE Consumer & Industrial
 Specialty Transformer
 PO Box 1701
 Ft. Wayne, IN 46801
 (260) 439-2000

GE MODEL #:
9T83C9464G13

Underwriters' Laboratories Inc Listed

RATING:

CU 3PH 60HZ 75.0KVA 480 +2,-4(2.5%TAPS) 208Y/120 NON-SIN K04

Frame = EE75
 Temp. Rise (C) = 115 Insulation System = 220C
 Average Sound Level (dB) = 50

LOSS DATA:

Max Core Loss or No Load Loss @ 100% voltage (Watts) =	560.0
Impedance Loss or Coil Loss @ Rise + 20C reference (Watts) =	<u>1,209.0</u>
Total Loss @ Rise + 20C reference (Watts) =	1,769.0

DIELECTRIC AND PRODUCTION TESTING:

Induce Test @ Twice rated voltage 400 Hz per ANSI C89.2 and NEMA ST-20
 Hipot Test for High Voltage winding to Low Voltage and Ground @ 4000 volts 60 Hz 60 Sec.
 Hipot Test for Low Voltage winding to High Voltage and Ground @ 2500 volts 60 Hz 60 Sec.
 Polarity additive in accordance with ANSI C89.2 and NEMA ST-20

EFFICIENCY:

Efficiencies at reference temperature of Rise + 20C (Calculated).

Load (%)	Efficiency (%)
35	at least 98.0

IMPEDANCE:

Impedance at reference temperature of Rise + 20C (Calculated).

%R =	1.5
%X =	3.1
%Z =	3.5

REGULATION:

Regulation at reference temperature of Rise + 20C (Calculated).

PF	Regulation (%)
1.0	1.6
0.8	3.1