



Transformer


Catalog Number 9T83W3876G80

150.0 KVA 60 HZ 3 PH 5.1 % IMP

40 C AMB. 80 C RISE 220 C SYSTEM IS-19C Type: QL

Note: Design is based on 225.0KVA & 150C Rise 7.8% Imp.


PRIMARY (H) 480 VOLTS (LINE-LINE)
 SECONDARY (X) 208 VOLTS (LINE-LINE)
 120 VOLTS (LINE-NEUTRAL)



JUMPER CONNECTION

TAP	VOLTS
1-2	500
2-3	494
3-4	480
4-5	467
5-6	454
6-7	440
7-8	427

COIL TAP ARRANGEMENT



NET WGT 1205 LB 546.6 Kg

081715 N534! L37AA
55557 NOG

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18W4322G88

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.



Outline: 303B912MWP177 INSPECTION & FINAL TEST
Assembled in Mexico N534!

