



GE Consumer & Industrial
Specialty Transformer
PO Box 1701
Ft. Wayne, IN 46801
(260) 439-2000

GE MODEL #:
9T83C9876G15

Underwriters' Laboratories Inc Listed

RATING:

CU 3PH 60HZ 150.0KVA 480 +2,-4(2.5%TAPS) 208Y/120

Frame = QF
Temp. Rise (C) = 115 Insulation System = 220C
Average Sound Level (dB) = 55

LOSS DATA @ 100% LOAD:

Core Loss or No Load Loss @ 100% voltage (Watts) =	1,170.0
Impedance Loss or Coil Loss @ Rise + 20C reference (Watts) =	<u>2,310.0</u>
Total Loss @ Rise + 20C reference (Watts) =	3,480.0

DIELECTRIC AND PRODUCTION TESTING:

Induce Test @ Twice rated voltage 400 Hz per ANSI C89.2 and NEMA ST-20

Hipot Test for High Voltage winding to Low Voltage and Ground @ 4000 volts 60 Hz 60 Sec.

Hipot Test for Low Voltage winding to High Voltage and Ground @ 2500 volts 60 Hz 60 Sec.

Polarity additive in accordance with ANSI C89.2 and NEMA ST-20

EFFICIENCY:

Efficiencies at reference temperature of Rise + 20C (Calculated).

Load (%)	Efficiency (%)
35	at least 98.3

IMPEDANCE:

Impedance at reference temperature of Rise + 20C (Calculated).

%R =	1.3
%X =	2.3
%Z =	2.6

REGULATION:

Regulation at reference temperature of Rise + 20C (Calculated).

PF	Regulation (%)
1.0	1.4
0.8	2.4