



Transformer



Catalog Number Type QL


9Q1C050AXAS00A5T00

9T83S2573

50.0 KVA 60 HZ 1 PH 4.5 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG



PRIMARY LINES ON H1-H2				SECONDARY LINES ON X1-X4	
VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT
215	8-H1, 7-H2	430	8-7	120	X1-X3, X2-X4
227	6-H1, 5-H2	442	7-6	240	X2-X3
240	4-H1, 3-H2	454	6-5		
253	2-H1, 1-H2	467	5-4		
		480	4-3		
		493	3-2		

NET WGT

500 LB

226.8 Kg



57981

101715

INSPECTION & FINAL TEST

N5421

COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18S4317G06

Outline: 303B406SAP073 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL



IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES

CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

X3 X1 - X2 X4 - -

- - H2 - - H1

Note: Standard



X4 - H1
X2 - H2
X1 - H2
X3 - H2
X4 - H1
X2 - H1
X1 - H2
X3 - H2