





Catalog Number **9T83W2570G80** TYPE **QL**

**15.0 KVA 60 HZ 1 PH 3.2 % IMP**

40 C AMB. 80 C RISE 220 C SYSTEM IS-19C

NOG





PRIMARY				SECONDARY	
LINES ON H1-H2				LINES ON X1-X4	
UOLTS	CONNECT	UOLTS	CONNECT	UOLTS	CONNECT
215	8-H1, 7-H2	431	8-7	120	X1-X3, X2-X4
229	6-H1, 5-H2	445	7-6	240	X2-X3
240	4-H1, 3-H2	458	6-5		
251	2-H1, 1-H2	469	5-4		
		480	4-3		
		491	3-2		
		502	2-1		

NET WGT  
350 LB  
158.8 Kg  
9T40G0007  
59140  
012716

INSPECTION  
&  
FINAL TEST  
N6051

COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18W4317G05

Outline: 303B406MWP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

X3 - X4 - X2 - X1  
- H2 - H1 - -

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Note: Standard

X1 - -  
X2 - -  
X3 - X4 - H1 - H1  
X3 - X4 - X2 - -  
X3 - H2 - H1 - -

