



Core & Coil Transformer



Catalog Number Type QL-C

9T84B2675

9T83W2675 9T83W2675 832675 150921KK
 E 303B932MWP075 YNNN 40150220IS-19CQL 1 60AL100109N100.0
 6.6 900 240x480(+2,-4 2.30%120/240 E1 I
 09T18W4322677615019NN 2FD3TDWMIDWEST 01475A1221EAG
 001 N01 NYF175MIDWEST2 100.000240x480(+2,-4 2.30%)
 120/240 0705NN9T83W2675 N9T18W43
 22677TRANSFORMER ENERGY8-NOG H0 0

NET WGT

775 LB

351.5 Kg

57742

092115

INSPECTION

&


FINAL TEST

N539!

100.0 KVA 60 HZ 1 PH 6.6 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C



NOG



51130000061000000

SECONDARY		PRIMARY	
LINES ON X1-X4	VOLTS CONNECT	LINES ON H1-H2	VOLTS CONNECT
	218	8-H1,7-H2	436
			8-7

COIL TAP ARRANGEMENT



LISTED 769G

Outline: 303B932AAP075 Assembled in Mexico

X3 X4 - X2 X1 - -

- - H2 - - H1

Note: Standard

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

X1 - - H1
 X2 - - H1
 X3 X4 - - H2
 X3 X4 - - H2

