



# Core & Coil Transformer




Catalog Number Type QL-C

9T84C2572

37.5 KVA 60 HZ 1 PH 5.1 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG



PRIMARY LINES ON H1-H2				SECONDARY LINES ON X1-X4	
VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT
218	8-H1, 7-H2	436	8-7	120	X1-X3, X2-X4
229	6-H1, 5-H2	447	7-6	240	X2-X3
240	4-H1, 3-H2	458	6-5		
251	2-H1, 1-H2	469	5-4		
		480	4-3		
		491	3-2		

NET WGT

460 LB

208.7 Kg



46436

110315

INSPECTION  
&  
FINAL TEST

N5451

COIL TAP ARRANGEMENT



Outline: 303B406AAP072 Assembled in Mexico

H2 X4 - H1 X1 - -

- - X3 - - X2

Note: Standard

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES

CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

H2 X4 - H1 X1 - -  
- - X3 - - X2

\*2M0000000\*  
\*3M0000000\*