



Core & Coil Transformer




Catalog Number Type QL-C

9T84C2574

75.0 KVA 60 HZ 1 PH 5.5 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG



PRIMARY LINES ON H1-H2				SECONDARY LINES ON X1-X4	
VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT
215	8-H1, 7-H2	430	8-7	120	X1-X3, X2-X4
230	6-H1, 5-H2	445	7-6	240	X2-X3
240	4-H1, 3-H2	460	6-5		
250	2-H1, 1-H2	470	5-4		
		480	4-3		
		490	3-2		

NET WGT
595 LB
269.9 Kg



32439

110315

INSPECTION
&
FINAL TEST

N5451

COIL TAP ARRANGEMENT




Outline: 303B406AAP074 Assembled in Mexico

X3 X4 - X2 X1 - -

- - H2 - - H1

Note: Standard



X1 - X2 - X3 - X4 - H1 - H2 - H1 - H2

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES

CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.