DEH41099 Rev. 1



A Series® Lighting Control Panelboards

A Series® Lighting Controller BACnet Protocol Implementation Conformance Statement

Date May 13, 2004

Vendor Name GE Consumer & Industrial

Product Name GE A Series® Lighting Controller

Product Model Number 10092046P1/P2
Product Version 3.32 Firmware

BACnet Protocol Revision 3

Product Description

The GE A Series Lighting Controller provides programmable capabilities for use in lighting applications. Hardware features may vary, but all products use the same BACnet firmware and communicate on a BACnet MS/TP network (some models also support Ethernet and BACnet/IP). All products support all BACnet capabilities indicated, unless otherwise noted.

		Device Profile			Ethernet
Product Description	Product Model	ASC	AAC	ВС	& IP
ROCB Lighting Controller (c/w Ethernet)	10092046P2		✓		✓
ROCB Lighting Controller	10092046P1		✓		

BACnet Standardized Device Profile (Annex L)

BACnet Device	Notes
☐ BACnet Operator Workstation (B-OWS)	
☐ BACnet Building Controller (B-BC)	
☑ BACnet Advanced Application Controller (B-AAC)	See product list above.
☐ BACnet Application Specific Controller (B-ASC)	
☐ BACnet Smart Sensor (B-SS)	
☐ BACnet Smart Actuator (B-SA)	

BACnet Interoperability Building Blocks Supported (Annex K)

BACnet Interoperability Building Block	Supported
Data Sharing	
Data Sharing-ReadProperty-A (DS-RP-A)	Ø
Data Sharing-ReadProperty-B (DS-RP-B)	Ø
Data Sharing-ReadPropertyMultiple-A (DS-RPM-A)	Ø
Data Sharing-ReadPropertyMultiple-B (DS-RPM-B)	Ø
Data Sharing-ReadPropertyConditional-A (DS-RPC-A)	
Data Sharing-ReadPropertyConditional-B (DS-RPC-B)	
Data Sharing-WriteProperty-A (DS-WP-A)	Ø
Data Sharing-WriteProperty-B (DS-WP-B)	Ø
Data Sharing-WritePropertyMultiple-A (DS-WPM-A)	
Data Sharing-WritePropertyMultiple-B (DS-WPM-B)	Ø
Data Sharing-COV-A (DS-COV-A)	Ø
Data Sharing-COV-B (DS-COV-B)	Ø
Data Sharing-COVP-A (DS-COVP-A)	
Data Sharing-COVP-B (DS-COVP-B)	
Data Sharing-COV-Unsolicited-A (DS-COVU-A)	Ø
Data Sharing-COV-Unsolicited-B (DS-COVU-B)	Ø
Scheduling	
Scheduling-A (SCHED-A)	\square
Scheduling-Internal-B (SCHED-I-B)	<u> </u>
Scheduling-External-A (SCHED-E-B)	<u> </u>
	Į.
Trending	
Trending-Viewing and Modifying Trends-A (T-VMT-A)	
Trending-Viewing and Modifying Trends-Internal-B (T-VMT-I-B)	
Trending-Viewing and Modifying Trends-External-B (T-VMT-E-B)	
Trending-Automated Trend Retrieval-A (T-ATR-A)	
Trending-Automated Trend Retrieval-B (T-ATR-B)	✓
Network Management	
Network Management-Connection Establishment-A (NM-CE-A)	☑
Network Management-Connection Establishment-B (NM-CE-B)	✓
Network Management-Router Configuration-A (NM-RC-A)	
Network Management-Router Configuration-B (NM-RC-B)	
Alarm and Event Management	
Alarm and Event-Notification-A (AE-N-A)	
Alarm and Event-Notification Internal-B (AE-N-I-B)	☑
Alarm and Event-Notification External-A (AE-N-E-B)	
Alarm and Event-ACK-A (AE-ACK-A)	
Alarm and Event-ACK-B (AE-ACK-B)	Ø
Alarm and Event-Alarm Summary-A (AE-ASUM-A)	
Alarm and Event-Alarm Summary-B (AE-ASUM-B)	Ø
Alarm and Event-Enrollment Summary-A (AE-ESUM-A)	
Alarm and Event-Enrollment Summary-B (AE-ESUM-B)	Ø
Alarm and Event-Information-A (AE-INFO-A)	
Alarm and Event-Information-B (AE-INFO-B)	Ø
Alarm and Event-LifeSafety-A (AE-LS-A)	
Alarm and Event-LifeSafety-B (AE-LS-B)	
Device Management	•
	\square
DEVICE MANAGEMENT-DYNAMIC DEVICE BINDING-A HJMLJJJB-A)	
Device Management-Dynamic Device Binding-A (DM-DDB-A) Device Management-Dynamic Device Binding-B (DM-DDB-B)	$\overline{\mathbf{A}}$

BACnet Interoperability Building Block	Supported
Device Management-Dynamic Object Binding-B (DM-DOB-B)	V
Device Management-DeviceCommunicationControl-A (DM-DCC-A)	
Device Management-DeviceCommunicationControl-B (DM-DCC-B)	\square
Device Management-Private Transfer-A (DM-PT-A)	$\overline{\square}$
Device Management-Private Transfer-B (DM-PT-B)	V
Device Management-Text Message-A (DM-TM-A)	V
Device Management-Text Message-B (DM-TM-B)	
Device Management-TimeSynchronization-A (DM-TS-A)	☑ ¹
Device Management-TimeSynchronization-B (DM-TS-B)	☑ ²
Device Management-UTCTimeSynchronization-A (DM-UTC-A)	☑ ¹
Device Management-UTCTimeSynchronization-B (DM-UTC-B)	☑ 2
Device Management-ReinitializeDevice-A (DM-RD-A)	
Device Management-ReinitializeDevice-B (DM-RD-B)	Ø
Device Management-Backup and Restore-A (DM-BR-A)	
Device Management-Backup and Restore-B (DM-BR-B)	Ø
Device Management-List Manipulation-A (DM-LM-A)	
Device Management-List Manipulation-B (DM-LM-B)	
Device Management-Object Creation and Deletion-A (DM-OCD-A)	
Device Management-Object Creation and Deletion-B (DM-OCD-B)	Ø
Device Management-Virtual Terminal-A (DM-VT-A)	
Device Management-Virtual Terminal-B (DM-VT-B)	

¹ Only supported by B-BC products. Based on the UTC setting in the Device object. When UTC is enabled, both DM-TS-A and DM-UTC-A is supported, otherwise only DM-TS-A is supported.

Segmentation Capability

Segmented Requests Supported	V	Window Size	1
Segmented Responses Supported	\square	Window Size	1

Standard Object Types Supported

Object-Type	Supported	Dynamically Creatable	Dynamically Deletable	Optional Properties Supported	Writable Properties
Analog Input	Ø	Ø	$\overline{\mathbf{V}}$	Description, Device Type, Reliability, Min Pres Value, Max Pres Value, Update Interval, Resolution, COV Increment	Object Name, Description, COV Increment, Present Value (conditional), Out of Service, Reliability (conditional)
Analog Output	Ø	Ø	Ø	Description, Device Type, Reliability, Min Pres Value, Max Pres Value, Resolution, COV Increment	Object Name, Description, Present Value, COV Increment, Relinquish Default, Out of Service, Reliability (conditional)
Analog Value	Ø	Ø	Ø	Description, Reliability, COV Increment	Object Name, Description, Present Value (conditional), COV Increment, Out of Service, Reliability (conditional), Units
Averaging					

² Based on the UTC setting in the Device object. When UTC is enabled, DM-UTC-B is supported. When UTC is disabled DM-TS-B is supported. Dates before January 1, 2000 or after December 31, 2099 will be ignored.

A Series® Lighting Controller

BACnet Protocol Implementation Conformance Statement

Object-Type	Supported	Dynamically Creatable	Dynamically Deletable	Optional Properties Supported	Writable Properties
Binary Input	Ø	Ø	Ø	Description, Device Type, Reliability, Active Text, Inactive Text, Change Of State Time, Change Of State Count, Time of State Count Reset	Object Name, Description, Polarity, Present Value (conditional), Out of Service, Reliability (conditional)
Binary Output	Ø	Ø	Ø	Description, Device Type, Reliability, Active Text, Inactive Text, Change Of State Time, Change Of State Count, Time of State Count Reset, Min On Time, Min Off Time	Object Name, Description, Present Value, Polarity, Relinquish Default, Min On Time, Min Off Time, Out of Service, Reliability (conditional)
Binary Value	Ø	Ø	Ø	Description, Reliability, Active Text, Inactive Text Description	Object Name, Description, Present Value (conditional), Out of Service, Reliability (conditional) Object Name, Description,
Calendar	Ø	Ø	Ø	Description	Date List
Device	<u>□</u>	N/A	N/A	Description, Location, APDU Seg Timeout, Time Synch Recipients, Max Master, Max Info Frames, Max Segments Accepted, Local Time, Local Date, UTC Offset, DST Status, Active COV Subscription, Backup Failure Timeout, Last Restore Time, Configuration Files	Object Name, Description, Location, Time Synch Recipients, UTC Offset, APDU Segment Timeout, APDU Timeout, Number of APDU Retries, Max Master, Max Info Frames
Event Enrollment	Ø	Ø	Ø	Description, Notification Class	Object Name, Description, Event Type, Event Parameters, Object Property Reference, Event Enable, Notification Class
File	Ø			Description	Object Name, Description, File Type, Archive
Group					1790,74011170
Life Safety Point					
Life Safety Zone					
Loop	Ø	Ø	Ø	Description, Reliability, Update Interval, Proportional Constant, Proportional Units, Integral Constant, Integral Units, Derivative Constant, Derivative Units, Bias, Maximum Output, Minimum Output, COV Increment	Object Name, Description, Action, Manipulated Var Ref, Controlled Variable Ref, Controlled Var Units, Setpoint, Setpoint Ref, Proportional Constant, Proportional Constant Units, Integral Constant, Derivative Constant, Bias, COV Increment, Out of Service, Present Value (conditional), Reliability (conditional)
Multistate Input	Ø	Ø	Ø	Description, Reliability, Device Type, State Text	Object Name, Description, Present Value (conditional), Out of Service, Reliability (conditional)
Multistate Output					

BACnet Protocol Implementation Conformance Statement

Object-Type	Supported	Dynamically Creatable	Dynamically Deletable	Optional Properties Supported	Writable Properties
Multistate Value	Ø	Ø	Ø	Description, Reliability, State Text	Object Name, Description, Present Value (conditional), Out Of Service, Reliability (conditional)
Notification Class	Ø	Ø	Ø	Description	Object Name, Description, Ack Required, Priority, Recipient List
Program	Ø	Ø	Ø	Description, Reliability, Description of Halt, Reason for Halt	Object Name, Description, Program Change, Out of Service, Reliability (conditional)
Schedule	Ø	Ø	Ø	Description, Weekly Schedule, Exception Schedule	Object Name, Description, Effective Period, Weekly Schedule, Exception Schedule, List of Object Property Reference, Priority for Writing
Trend Log	Ø	Ø	Ø	Description, Start Time, Stop Time, Log Device Object Prop, Log Interval, COV Resubscription Interval, Notification Threshold, Records Since Notification, Notification Class, Event Enable, Acked Transition, Notify Type, Event Time Stamps	Object Name, Description, Log Enable, Start Time, Stop Time, Log Device Object Prop, Log Interval, Stop When Full, Buffer Size, Record Count
Proprietary	V	Ø	Ø		

Range Restrictions

Object-Type	Property	Range Restriction
All Object Types	Object Name	[1, 67] printable ASCII characters, inclusive
Binary Input, Binary Output	Change Of State Count	Accepts writes of value zero only
Loop	Bias	[0.0, 100.0] inclusive
Calendar	Date List	BACnet Date
Schedule	Exception Schedule	Will accept dates that include any wild combinations in the individual fields (example: unspecified day of week, unspecified day of month, January, unspecified year)
		Will not accept Start/End dates that include wild combinations in the individual fields (example: unspecified day of week, unspecified day of month, unspecified month, year 2004). Will accept Start/End dates in which all individual fields are wild (example: unspecified day of week, unspecified day of month, unspecified month, unspecified year). Will not accept DateRanges in which both the Start and End date are wild.
		WeekNDay Will accept dates that include any wild combinations in the individual fields (example: Mondays, unspecified week of month, December)
Schedule	Effective Period	End Date > Start Date (End date must be later date than the Start Date)

A Series® Lighting Controller

BACnet Protocol Implementation Conformance Statement

Data Link Layer Options

Options	Notes
☑ BACnet IP, (Annex J)	Only supported by Ethernet-capable products.
☑ BACnet IP, (Annex J), Foreign Device	Only supported by Ethernet-capable products.
☑ ISO 8802-3, Ethernet (Clause 7) (10Base2, 10Base5, 10BaseT, Fiber)	Only supported by Ethernet-capable products.
☐ ANSI/ATA 878.1, 2.5 Mb. ARCNET (Clause 8)	
☐ ANSI/ATA 878.1, RS-485 ARCNET (Clause 8), baud rate(s):	
☑ MS/TP master (Clause 9), baud rate(s): 9600, 19200, 38400, 76800	
☐ MS/TP slave (Clause 9), baud rate(s):	
☑ Point-To-Point, EIA 232 (Clause 10), baud rate(s): 9600, 1920, 38400	
☑ Point-To-Point, modem, (Clause 10), baud rate(s): 9600, 19200, 38400	
☐ LonTalk, (Clause 11), medium:	
☐ Other:	

Device Address Binding

Is static device binding supported?	☑ Yes	□ No
(Necessary for two-way communication	with MS/	TP slaves and certain other devices.)

Networking Options

Router	Ø	Router between Ethernet, BACnet/IP, MS/TP and PTP or between MS/TP and PTP (model dependent).
Annex H, BACnet Tunneling		
BACnet/IP Broadcast Management Device (BBMD)		
Does the BBMD support registrations by Foreign Devices?		

Character Sets Supported

Indicating support for multiple character sets does not imply that they can all be supported simultaneously.

☑ ANSI X3.4	☐ IBM/Microsoft DBCS	□ JIS C 6226
☐ ISO 10646 (ICS-4)	☐ ISO 10646 (UCS2)	☐ ISO 8859-1

If this product is a communication gateway, describe the types of non-BACnet equipment/networks(s) that the gateway supports

Not applicable.



GE Consumer & Industrial