



# Transformer



\*1M0000000\*

Catalog Number


TYPE QL

9T83W3624

75.0 KVA 60 HZ 3 PH 5.3 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

Note: Design is based on 75.00KVA & 150C Rise 5.3% Imp.



JUMPER CONNECTION	
TAP	VOLTS
1	629
2	615
3	600
4	585
5	571
6	556
7	542

NET WGT

620 LB

281.2 Kg

9T40G0007

55627

XV374

NOG


092415

INSPECTION & FINAL TEST N539!

PRIMARY (H) 600 VOLTS (LINE-LINE)

SECONDARY (X) 480 VOLTS (LINE-LINE)

### COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18W4317G06

Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

Outline: 303B401MWP074

ALUMINUM CONDUCTOR

PRIMARY: 10 KV BIL

SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

X3 - X2 - X1 - -  
- H3 - H2 - H1

Note: Standard

X1 - -  
X2 - - H1  
X3 - - H2 - H1  
X1 - -  
X2 - - H2 - H1  
X3 - - H3 - H1



\*2M0000000\*



\*3M0000000\*