



Industrial Solutions

Molded Case Circuit Breaker

Current Ratings

40, 45, 50, and 60 Amperes

Voltage Ratings (Max.)

1-pole – 277 Vac (125 Vdc)

2- and 3-pole – 480 Vac (250 Vdc)

Frequency Ratings

60 Hertz

Type TEYD, TEYH, TEYL, 40-60 Amperes
Enclosure Compensated

Long-time Delay and Instantaneous
Time-current Curves

Curves show enclosure-compensated circuit breaker in open air, 40°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use rating shift index at top of sheet.

DES080

Adjustments

Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.

by **ABB**