



# Transformer


Catalog Number 9T83W3877G80

225.0 KVA    60 HZ    3 PH    5.1 % IMP

40 C AMB.    80 C RISE    220 C SYSTEM    IS-19C    Type: QL


Note: Design is based on 300.0KVA & 150C Rise 6.9% Imp.

PRIMARY (H)    480 VOLTS (LINE-LINE)  
 SECONDARY (X)    208 VOLTS (LINE-LINE)  
                           120 VOLTS (LINE-NEUTRAL)



JUMPER CONNECTION	
TAP	VOLTS
1-2	506
2-3	493
3-4	480
4-5	468
5-6	455
6-7	442
7-8	430

### COIL TAP ARRANGEMENT



NET WGT 1470 LB    666.8 Kg

081715    N534!    L38AA  
                           55562    NOG

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18W4322G88

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
 ALUMINUM CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES  
 CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.



LISTED 769G

Outline: 303B912MWP178  
 Assembled in Mexico

INSPECTION & FINAL TEST  
 N534!

