

PowerMark Gold™ Meter Socket Load Center 125-200 Amp, 4 Circuit

- Ringless 125-200 Amp MSLC
 - Horn bypass
 - Feed-thru lugs standard
 - Factory installed main breaker
 - Approved for Xcel Energy utility
 - Meets EUSERC specifications
 - Combination flush/surface type mounting
-
- Single phase, three wire, 120/240 VAC, 22 kAIC rated
 - UL Listed (UL Standards No. 67 for Panelboards)
 - 60°C/75°C conductor rating
 - Suitable for use as Service Entrance Equipment when installed in accordance with the National Electrical Code




PowerMark Gold™ Meter Socket Load Center
200 Amp 4 Circuit


Catalog Number	TSMR412CSCU, TSMR415CSCU, TSMR420CSCU
Main Amp Rating	125A, 150A, 200A
Enclosure Type	Outdoor (NEMA 3R)
Front Type	Surface
Bypass	Horn Bypass
Agency Certification	UL
Compliance	EUSERC
Utility Incoming	OH / UG
Service Disconnect	THQMV Breaker Factory Installed
Equipment Ground Kit	TGK12 Factory Installed

1" Spaces		1/2" Spaces		Total 1 Pole Spaces	Box R31 Enclosure Dimensions (inches)			Main Wire Size (AWG/kcmil) Cu-Al
1 Pole	2 Pole	1 Pole	2 Pole		Width	Height	Depth	
4	2	8	3	8	14 9/16	33 9/16	6 3/16	6-350

Knockouts



	Symbol				
	A	B	C	L	R
Conduit Size in Inches	9/32	—	—	—	—
	—	—	3/8	—	—
	—	1/2	1/2	—	—
	—	—	3/4	—	—
	—	—	—	1	—
	—	—	—	1 1/4	—
	—	—	—	1 1/2	1 1/2
	—	—	—	—	2
	—	—	—	—	2 1/2



Breaker Symbol	Breaker Fill	
	1" THQL	1/2" THQP
	1	—
	1	2

GE Consumer & Industrial
41 Woodford Avenue, Plainville, CT 06062
www.geelectrical.com
© 2006 General Electric Company

