



DOE 2016 Transformers

9T	1	0	A	100	1	G31
-----------	----------	----------	----------	------------	----------	------------

GE Standard	Group Number
1 = QL DOE 2016 Design	No Group Number Shown = 150°C
Transformer Type	G02 = 150°C, -3dB
0 = Standard, K1	G03 = 150°C, Electrostatic Shield†
1 = K13*	G04 = 150°C, Electrostatic Shield†, -3dB
2 = K20*	G05 = 150°C, -5dB
3 = K30*	G06 = 150°C, Electrostatic Shield†, -5dB
4 = K4*	G09 = 150°C, Non-STD kVA
7 = Guard II/Servicenter	G10 = 150°C, Non-STD kVA
8 = Spare Parts	G29 = 140°C, 40°C amb
Coil Material	G30 = 140°C, 50°C amb
A = Aluminum	G31 = 115°C
C = Copper	G32 = 115°C, -3dB
	G33 = 115°C, Electrostatic Shield†
	G34 = 115°C, Electrostatic Shield†, -3dB
	G35 = 115°C, -5dB
	G36 = 115°C, Electrostatic Shield†, -5dB
	G39 = 115°C, Non-STD kVA
	G40 = 115°C, Non-STD kVA
	G61 = 80°C
	G62 = 80°C, -3dB
	G63 = 80°C, Electrostatic Shield†
	G64 = 80°C, Electrostatic Shield†, -3dB
	G65 = 80°C, -5dB
	G66 = 80°C, Electrostatic Shield†, -5dB
	G69 = 80°C, Non-STD kVA
	G70 = 80°C, Non-STD kVA

kVA Rating
1 = 15kVA
2 = 30kVA
3 = 45kVA
4 = 75kVA
5 = 112.5kVA
6 = 150kVA
7 = 225kVA
8 = 300kVA
9 = 500kVA

Voltage Rating
See Voltage Chart on back page

*All K-factor transformers contain an electrostatic shield. Therefore, when creating new K-factor product numbers, be sure to select a Group Number that includes an electrostatic shield. Example: 9T11C1001 is incorrect. 9T11C1001G03 is correct. 9T14A1004G05 is incorrect. 9T14A1004G06 is correct.

†An Electrostatic Shield (also called a Guard I transformer) is a grounded, aluminum-foil barrier between the primary and secondary winding to reduce electrical noise.

GE Transformers TP-1 to DOE 2016 Product Number Conversion Guide K Factor =1, 480 Volts Primary, 208Y/120 Volts Secondary, Standard Sound Level

NEMA TP-1	Coil Material**	ES Shield	KVA	Temp Rise	DOE 2016
9T83B3871	AL	N	15	150	9T10A1001
9T83B3871G03	AL	Y	15	150	9T10A1001G03
9T83B3871G15	AL	N	15	115	9T10A1001G31
9T83B3871G13	AL	Y	15	115	9T10A1001G33
9T83B3871G80	AL	N	15	80	9T10A1001G61
9T83B3871G83	AL	Y	15	80	9T10A1001G63
9T83B3872	AL	N	30	150	9T10A1002
9T83B3872G03	AL	Y	30	150	9T10A1002G03
9T83B3872G15	AL	N	30	115	9T10A1002G31
9T83B3872G13	AL	Y	30	115	9T10A1002G33
9T83B3242G80	AL	N	30	80	9T10A1002G61
9T83B3872G83	AL	Y	30	80	9T10A1002G63
9T83B3873	AL	N	45	150	9T10A1003
9T83B3873G03	AL	Y	45	150	9T10A1003G03
9T83B3873G15	AL	N	45	115	9T10A1003G31
9T83B3873G13	AL	Y	45	115	9T10A1003G33
9T83B3873G80	AL	N	45	80	9T10A1003G61
9T83B3873G83	AL	Y	45	80	9T10A1003G63
9T83B3874	AL	N	75	150	9T10A1004
9T83B3874G03	AL	Y	75	150	9T10A1004G03
9T83B3874G15	AL	N	75	115	9T10A1004G31
9T83B3874G13	AL	Y	75	115	9T10A1004G33
9T83B3874G80	AL	N	75	80	9T10A1004G61
9T83B3874G83	AL	Y	75	80	9T10A1004G63
9T83B3875	AL	N	112.5	150	9T10A1005

NEMA TP-1	Coil Material**	ES Shield	KVA	Temp Rise	DOE 2016
9T83B3875G03	AL	Y	112.5	150	9T10A1005G03
9T83B3875G15	AL	N	112.5	115	9T10A1005G31
9T83B3875G13	AL	Y	112.5	115	9T10A1005G33
9T83B3875G80	AL	N	112.5	80	9T10A1005G61
9T83B3875G83	AL	Y	112.5	80	9T10A1005G63
9T83B3876	AL	N	150	150	9T10A1006
9T83B3876G03	AL	Y	150	150	9T10A1006G03
9T83B3876G15	AL	N	150	115	9T10A1006G31
9T83B3876G13	AL	Y	150	115	9T10A1006G33
9T83B3876G80	AL	N	150	80	9T10A1006G61
9T83B3876G83	AL	Y	150	80	9T10A1006G63
9T83B3877	AL	N	225	150	9T10A1007
9T83B3877G03	AL	Y	225	150	9T10A1007G03
9T83B3877G15	AL	N	225	115	9T10A1007G31
9T83B3877G13	AL	Y	225	115	9T10A1007G33
9T83B3877G80	AL	N	225	80	9T10A1007G61
9T83B3877G83	AL	Y	225	80	9T10A1007G63
9T83B3878	AL	N	300	150	9T10A1008
9T83B3878G03	AL	Y	300	150	9T10A1008G03
9T83B3878G15	AL	N	300	115	9T10A1008G31
9T83B3878G13	AL	Y	300	115	9T10A1008G33
9T83B3878G80	AL	N	300	80	9T10A1008G61
9T83B3878G83	AL	Y	300	80	9T10A1008G63
9T83B3879	AL	N	500	150	9T10A1009
9T83B3879G03	AL	Y	500	150	9T10A1009G03

**For DOE 2016 copper coil product numbers, change "A" to "C".
Example: 9T10A1004 changes to 9T10C1004.



GE DOE 2016 Transformers Feature...

- Outward facing mounting feet for faster installation
- Lug kit included up to 150kVA
- Copper ground bar kit included
- Larger interior clearances for easier wiring & enhanced safety

3-Phase Common Voltages

Series	Primary Voltage	Secondary Voltage
100	480	208Y/120
101	480	220
102	480	220Y/127
103	480	208
104	480	230Y/133
105	480	240Y/139
106	480	380
107	480	380Y/219
108	480	400Y/231
109	480	415Y/240
110	480	480
111	480	575
112	480	600
113	480	440Y/254
114	480	600Y/346
115	480	440
116	480	230/115
117	480	480Y/277
118	480	240/120
119	480	240
121	480	220/110
123	480	400
124	480	460
125	480	420
126	480	230
127	480	575Y/332
129	480	460Y/266
131	208	240
132	208	240/120
133	208	480
134	208	480Y/277
135	208	380Y/219
136	208	230
137	208	575
138	208	460
139	208	400Y/231
140	208	208
141	208	230Y/133
142	208	380
143	208	220/110
144	208	220Y/127
145	208	208Y/120
146	208	400
147	208	315
148	208	600
149	208	460Y/266
150	208	220
151	208	230/115
152	208	415Y/240
153	240	480Y/277
154	240	480
155	240	400Y/231
157	240	575
158	240	460Y/266
159	240	240Y/139
160	240	600
161	240	208Y/120
162	240	380
163	240	440
164	240	240/120
165	240	380Y/219
166	220	380Y/219
167	220	400Y/231
168	220	240Y/139
169	220	220
170	220	208Y/120

Series	Primary Voltage	Secondary Voltage
171	220	480Y/277
172	220	440Y/254
173	220	480/240
174	220	480
175	220	415Y/240
176	380	220Y/127
177	380	480
178	380	220
179	380	208Y/120
180	380	415Y/240
181	380	240/120
184	380	480Y/277
185	380	380Y/219
186	380	230Y/133
187	380	240
188	440	220Y/127
189	440	480
190	440	208Y/120
191	440	380
192	440	380Y/219
193	440	400Y/231
194	440	575Y/332
195	440	240/120
196	440	480Y/277
197	440	240
198	230	460
199	230	400Y/231
200	230	400
201	230	480Y/277
202	230	208Y/120
203	230	480
204	400	230Y/133
205	400	380Y/219
206	400	480
207	400	220Y/127
209	400	400Y/231
210	400	208Y/120
211	400	208Y/120
212	400	480Y/277
213	415	208Y/120
214	415	460
215	415	220Y/127
216	416	208Y/120
217	416	480Y/277
218	460	208Y/120
219	460	220
221	460	400Y/231
222	460	220Y/127
223	460	230
224	460	575Y/332
225	460	230Y/133
226	460	460Y/266
227	550	208Y/120
228	550	480Y/277
229	575	208Y/120
230	575	480Y/277
231	575	240Y/139
232	575	460
233	575	480
234	575	230Y/133
235	575	230
236	600	240/120
237	600	480
238	600	480Y/277
239	600	240
240	600	208Y/120

Series	Primary Voltage	Secondary Voltage
241	600	230Y/133
242	600	240Y/139
243	600	208
244	600	600Y/346
247	277	415Y/240
248	315	208Y/120
249	320	480Y/277
250	420	480Y/277
251	490	480Y/277
252	500	480Y/277
253	480	450
254	277	208Y/120
255	460	240/120
256	240	240
257	208	240Y/139
258	220	380
259	480	320Y/185

3P Servicenter Product Numbers - DOE 2016

Material	KVA	Primary Voltage	Secondary Voltage	Product Number
AL	15	240	208Y/120	9T17A0001
	22.5	240	208Y/120	9T17A0002
	30	240	208Y/120	9T17A0003
	15	480	208Y/120	9T17A0011
	22.5	480	208Y/120	9T17A0012
	30	480	208Y/120	9T17A0013
	15	600	208Y/120	9T17A0021
	22.5	600	208Y/120	9T17A0022
	30	600	208Y/120	9T17A0023
	CU	15	240	208Y/120
22.5		240	208Y/120	9T17C0005
30		240	208Y/120	9T17C0006
15		480	208Y/120	9T17C0014
22.5		480	208Y/120	9T17C0015
30		480	208Y/120	9T17C0016
15		600	208Y/120	9T17C0024
22.5		600	208Y/120	9T17C0025
30		600	208Y/120	9T17C0026

For NEMA 3R 316 stainless steel enclosure, replace the "A" or "C" in the Product Number with "S".

Guard II Product Numbers - DOE 2016

Material	KVA	Primary Voltage	Secondary Voltage	Product Number
AL	15	480	208Y/120	9T17A1001G03
	30	480	208Y/120	9T17A1002G03
	45	480	208Y/120	9T17A1003G03
	75	480	208Y/120	9T17A1004G03
	112.5	480	208Y/120	9T17A1005G03
CU	15	480	208Y/120	9T17C1001G03
	30	480	208Y/120	9T17C1002G03
	45	480	208Y/120	9T17C1003G03
	75	480	208Y/120	9T17C1004G03
	112.5	480	208Y/120	9T17C1005G03

GE Energy Connections
41 Woodford Avenue
Plainville, CT 06062
1-800-431-7867
www.geindustrial.com

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, express or implied, that such performance will be obtained under end-use conditions. ©2018, General Electric Company and/or its affiliates. All rights reserved.

4.18 DET-851E

