


Product brochure

Conceptpower DPA 500 480V UL – Modular UPS 100kW – 3MW





## Conceptpower DPA 500 The modular UPS for medium-sized and large data centers



Today's data centers require continuous uptime. That target is why ABB's Conceptpower DPA 500 is based on Decentralized Parallel Architecture (DPA). Only a truly redundant architecture like DPA allows online modules to be swapped out while the system is running. Each high-reliability, standardized module is self-contained and can be swapped at any time, so no load

### Maximized availability

### **Key benefits**

- 99.9999% availability
- Decentralized parallel architecture
- Replace or add modules with no downtime
- Short mean-time-to repair
- No single points of failure

### Cost effective "right-sizing"

### Key benefits

- Scalable from 100kW up to 3MW
- Optimized cabinets available in 300kW and 500kW
- Vertical and horizontal scalability
- Pay as you grow

has to be ever switched off – making routine maintenance safe and easy. Conceptpower DPA 500 is designed to secure continuity of critical operations for data centers, colocations, server rooms and other IT applications. It also protects industrial automation processes, healthcare facilities and many other vertical markets where operations are of a critical nature.

#### Low total cost of ownership

Key benefits
-> 96% true online efficiency
- Small footprint/high power density
– Unity power factor (kW = kVA)
– Low input harmonic distortion (THDi < 3.5%)
Efficient service concept
Key benefits
- Simple power upgrade
– Fast service – Iow MTTR

- Reduced spare parts needed
- Online-swap modularity (OSM)
- Online serviceability

# The lowest total cost of ownership

The Conceptpower DPA 500 boasts a low cost of ownership compared to other UPS systems by offering energy efficiency, scalability and ergonomic design to enable easy serviceability.

It can be sized to align closely with prevailing IT requirements, but can be added to incrementally as IT needs grow. This means that you only power and cool what you need. The resulting savings in power usage over the service life of the UPS are substantial.

Rack-mounted configurations can be right-sized by inserting or removing 'online-swappable' modules while the systems remain online, enabling power to be added as requirements grow without any footprint penalty. This makes servicing simple as modules can be replaced without powering down.

Together with the excellent efficiency rating (> 96%) of the product, all these factors gives the Conceptpower DPA 500 the lowest total cost of ownership of any similar UPS system.



### Sized to fit your needs

Designers often over-specify UPS systems to take account of future demand growth. With the Conceptpower DPA 500, modules can simply be added in parallel to increase the system's total capacity. The Conceptpower DPA 500's vertical and horizontal scalability allows:

- Flexible power upgrades and downgrades
- Easy maintenance
- Pay as you grow



### Protecting power has never been easier

True, online-swap modularity enables the safe removal and/or insertion of Conceptpower DPA modules without risk to the critical load and without the need to power down or transfer to raw mains supply. This unique feature directly addresses today's requirement for continuous uptime. The ability to online-swap modules in a Conceptpower DPA system significantly reduces its mean time to repair (MTTR) and simplifies system upgrades. The modular approach pays off too when it comes to serviceability and availability – online-swapping of modules means you don't have to switch off or switch to bypass during replacements, so there is no downtime in a redundant configuration.

Installation and service is easy too: The straightforward concept of the Conceptpower DPA simplifies every step of the deployment process, from planning, through installation and commissioning to full use. Flexible set-up and fast maintenance means lower operating and maintenance costs. The UPS is serviceable by front access only.

## Total vertical and horizontal scalability

The Conceptpower DPA 500 delivers power protection from 100kW up to 3MW. With two optimized cabinet solutions, of up to 300 and 500kW respectively, these can operate in a parallel configuration to build the UPS system with both vertical and horizontal scalability. This means that there is no need to over specify the original configuration as power modules can simply be added, as needed, in the future.




=3MW

5×6×100kw

## Designed with maximum flexibility and redundancy at its core for the standardization of power protection.

In a data center, power distribution systems have historically been oversized to meet the redundancy requirements. The Conceptpower DPA 500 UPS was designed for datacenters and other high power applications that require redundant configurations (for example N+1, 2 (N+1), etc.). Adding redundancy for increased availability comes easy with the advanced scalability within the Conceptpower DPA 500 UPS. Conceptpower DPA 500 complements and completes the datacenter power distribution system for ABB, providing customers with a centralized power protection solution.



### Centralized power protection solutions

N = Conceptpower DPA 500 480V UL

Sample reference scenario of ABB's centralized power protection solution, Tier 4 data center 2(N+1) UPS configuration

# Compact cabinet designs provide added flexibility

## True parallel architecture

This advanced UPS design provides the highest degree of protection in critical applications where the load must be fed with quality power. The Conceptpower DPA 500 utilizes decentralized parallel architecture and ensures the highest level of reliability and availability with true redundancy across modules.

Each module operates independently, containing all hardware and software required for full system operation, creating complete redundancy within the unit. Each UPS module has its own independent static bypass, rectifier, inverter, logic control, control panel and battery charger. With all the critical components duplicated and distributed between individual units, potential single points of failure are eliminated.

### Basic system configuration

### The module includes:


- 100kW rated power module
- True online double conversion UPS
- Built-in modular isolation
- Built-in backfeed protection
- Individual module display
- HMI interface with mimic diagram and LCD providing information in five languages

### The cabinet includes:

- Optimized cabinets, with either 300 or 500kW of rated power
- Top or bottom cable entry (standard)
- Rectifier, bypass terminals (single or dual-input mains connection available) and UPS output terminals
- Battery breakers and output switches for each module set
- Graphical color touch screen system display
- Communication interfaces: RS-232 and USB ports, I/O dry contacts (e.g. EPO, GEN On) and external bypass interlock


### **Options**

- Centralized MCS / MCCB\*
- Battery monitoring
- Dual input feed
- Seismic bracing
- Maintenance bypass cabinet\*
- Control and monitoring (Modbus RS-485, Modbus TCP/IP, SNMP, Bacnet and others)
- Line-and-match battery cabinets
- \* Available for some models. Please contact factory for availability.



### 300kW cabinet

Capacity	Up to three modules
Parallel capability	Up to 4 cabinets in parallel (1.2MW)



### 500kW cabinet

Capacity	Up to five modules	
Parallel capability	Up to 6 cabinets in parallel (3MW)	

# Technical specifications

GENERAL DATA	-	<del>,</del>	
	300kW cabinet	500kW cabinet	
System power range	100kW – 1.2MW	100kW – 3MW	
Nominal power/module	100kW	,	
Nominal power/cabinet (capacity)	300kW	500kW	
Output power factor	1.0		
Topology	Double conversion, transformerless, modular, Decentralized	Parallel Architecture	
Parallel configuration	Up to 3 modules in one cabinet (300kW)/up to 4 cabinets in parallel (1.2MW)	Up to 5 modules in one cabinet (500kW)/up to 6 cabinet in parallel (3MW)	
Cable entry	Bottom or top as standard		
Serviceability	Front access only		
Back-feed protection	Built-in as (standard)		
INPUT			
Nominal input voltage	3 x 480V + G		
Voltage tolerance	± 10%		
nput distortion THDi	< 3.5% at 100% load		
Frequency range	60Hz ± 5%		
Power factor	0.99 @ 100% load		
Walk in/soft start	Yes		
OUTPUT	i		
Rated output voltage	3 x 480 V		
Voltage tolerance	$< \pm 1\%$ with static load/ $< \pm 4\%$ with step load (referred to 480V)		
/oltage distortion	± 1.5%		
Frequency	60 Hz		
EFFICIENCY			
AC-AC	> 96% (at nominal load)		
ENVIRONMENT			
Protection rating	IP 20		
Storage temperature	-25° to +70°C		
Operating temperature	0° to +40°C		
Altitude (above sea level)	1000 m without de-rating		
BATTERIES	6		
Number of 12V jars/string	45 jars (540V nominal)		
Гуреs	VRLA, vented lead-acid, NiCd		
Battery charger	Decentralized charger in each module set		
COMMUNICATIONS	5		
User interface	Graphical touch screen (one per cabinet as standard)		
Openne velocitor e + -	Decentralized LCD + mimic diagram (one per module as standard)		
Communication ports	USB, RS-232, voltage-free contacts, SNMP (optional)		
Customer interface	Remote shutdown, gen-set interface, external bypass conta	act	
Safety	UL 1778 5th edition, CSA C22.2 No. 107.3-14 Third Edition		
EMC	IEC/EN 62040-2 C3		
Manufacturing	ISO 9001:2008		
WEIGHT, DIMENSIONS	· · · · · · · · · · · · · · · · · · ·	f	
Weight	1944 lbs. (882 kg)	2150 lbs. (975 kg)	
Dimensions WxHxD	53" x 77.75" x 36" (1347 x 1975 x 914 mm)	70" x 77.75" x 36" (1778 x 1975 x 914 mm)	

### Contact us

**Power Protection** 

5900 Eastport Boulevard Richmond, VA 23231-4453 USA Tel: +1 800 292 3739 Fax: +1 804 236 4047

www.abb.com/ups ric.sales@us.abb.com We reserve the right to make technical changes to the product and to the information in this document without notice. The agreed conditions at the time of the order shall apply. ABB assumes no responsibility for any errors or omissions that may appear in this document. We reserve all rights in this document and in the information contained therein. Without prior written approval from ABB, reproduction, disclosure to third parties or use of any information, in whole or in part, is strictly forbidden.

© Copyright 2017 ABB, all rights reserved.



020317

