



Core & Coil Transformer




Catalog Number Type QL-C

9T84B2674

75.0 KVA 60 HZ 1 PH 6.2 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG



PRIMARY LINES ON H1-H2				SECONDARY LINES ON X1-X4			
VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT
216	8-H1, 7-H2	432	8-7	120	X1-X3, X2-X4		
230	6-H1, 5-H2	446	7-6	240	X2-X3		
240	4-H1, 3-H2	460	6-5				
250	2-H1, 1-H2	470	5-4				
		480	4-3				
		490	3-2				

NET WGT
470 LB
213.2 Kg



35851

102715

INSPECTION
&
FINAL TEST

N544I


COIL TAP ARRANGEMENT



Outline: 303B406AAP074 Assembled in Mexico

X3 X4 - X2 X1 - -
- - H2 - - H1

Note: Standard



X1 - - H1
X2 - - H2
X3 - - H2
X4 - - H1

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.