

Compact Power Line

CP2000AC54SD Front-End Power Supply

Input: 200-240 Vac; Outputs: ± 54 Vdc at 2000W; 5 Vdc at 4W



Applications

- 48Vdc distributed power architectures
- Power over Ethernet
- Routers/Switches
- VoIP/Soft Switches
- LAN/WAN/MAN applications
- File servers
- Indoor wireless
- Telecommunications equipment
- Enterprise Networks
- SAN/NAS/iSCSI applications
- Advanced workstations

Features

- Compact 1-RU form factor providing 20 W/in³
- 2000W from nominal 200 – 240 Vac
- Programmable output voltage
- PMBus compliant I²C and RS485 serial bus communications
- Power factor correction (meets EN/IEC 61000-3-2 and EN 60555-2 requirements)
- DC Output over-voltage and over-current protection
- AC Input over-voltage and under-voltage protection
- Over-temperature warning and protection
- Redundant, parallel operation with active load sharing and redundant +5V Aux power
- Remote ON/OFF
- Hot insertion/removal (hot plug)
- Four front panel LED indicators
- UL* Recognized to UL60950-1, CAN/ CSA[†] C22.2 No. 60950-1, and VDE[‡] 0805-1 Licensed to IEC60950-1
- CE mark meets 2006/95/EC directive[§]
- Internally controller variable-speed fan

The CP2000AC54SD Front-End Power Supply in the Compact Power Line platform is specifically designed to operate as an integral part of a complete distributed power system. The high-density, front-to-back airflow rectifier is designed for minimal space utilization and is highly expandable for future growth. It is provided with many features including RS485 and I²C communications busses that allow it to be used in a broad range of applications. The flexible feature set makes this front-end power supply an excellent choice for applications requiring modular ac-to-dc bulk intermediate voltages, such as in distributed power.

* UL is a registered trademark of Underwriters Laboratories, Inc.

† CSA is a registered trademark of Canadian Standards Association.

‡ VDE is a trademark of Verband Deutscher Elektrotechniker e.V.

§ This product is intended for integration into end-user equipment. All the required procedures for CE marking of end-user equipment should be followed. (The CE mark is placed on selected products.)

** ISO is a registered trademark of the International Organization of Standards.

Specifications

| Input | | | | | |
|--|------------|-------------|------------|--------------|--|
| Parameter | Min | Typ | Max | Units | Notes |
| Operating Voltage Range 2000W Configuration | 175 | 200/240 | 275 | Vac | May not meet all requirements, but will maintain output regulation. May shut down but will not get damaged. |
| Permitted Excursions | 275 | | 300 | | |
| Surges | 300 | | 325 | | |
| Input Frequency | 47 | | 63 | Hz | |
| Input Current | | 11.8 9.9 | | A | At 200 Vac At 240 Vac |
| Inrush Transient | | 25 | | Apk | Measured at 25°C for all line conditions; does not include X-Capacitors charging. |
| Input Leakage Current | | 1.5 | | mA | Measured at 265Vac, 60Hz |
| Power Factor | | 0.98 | | | From 50% to 100% load. |
| Efficiency | | 90 | | % | At 230 Vac with Vout > 52V and Pout > 50%. |
| Holdup Time | | 15 | | ms | Measurement starts at zero crossing of the ac voltage. Alarm issued via PFW signal going LO 5 ms prior to output voltages going out of limits. Measurements made at 65% full load and voltage allowed to decay to 49.5V. |

| Main Output | | | | | |
|-------------------------|------------|------------|------------|--------------|---|
| Parameter | Min | Typ | Max | Units | Notes |
| Maximum Output Power | | | 2000 | W | |
| Output Voltage Setpoint | | 54 | | Vdc | Output floats with respect to frame ground. |
| Setpoint Accuracy | -1 | | +1 | % | |
| Overall Regulation | -2 | | +2 | % | Includes all variations due to specified load range, drift, and environmental conditions. |
| Output Voltage Range | 44 | | 58 | Vdc | Analog margining. |
| | 42 | | 58 | Vdc | Set either by I ² C, RS485 |
| Maximum Output Current | | | 37 | A | @ 54Vdc |
| Current Share | | | 10 | %FL | Single-wire connection. Maintains tolerance to average of all other rectifiers. |

Specifications (continued)

| Output (continued) | | | | | |
|---|-------------|---------------|-----------------|---------------------------|---|
| Parameter | Min | Typ | Max | Units | Notes |
| Output Ripple RMS (5Hz to 20MHz) Peak-to-Peak (5Hz to 20MHz) Psophometric Noise | | | 250 500 2 | mVrms mVpk-pk mVrms | Measured with 20MHz bandwidth under any condition of loading. Minimum load is 1A. |
| External Bulk Load Capacitance | 0 | | 5,000 | μF | External capacitance can be increased but the power supply will not meet its turn-ON rise time requirement. |
| Turn-On Delay Rise Time ¹ - Standard (PMBus) - Telecom (RS-485) ² Overshoot | | 5 100 5 | | s ms s % | Monotonic Turn-On after detection of valid ac voltage. Measured from 30% to 100% of Vnom. Customer-selectable turn-on, either standard or with current walk-in, see Protocol Select under Signal Definitions. |
| Load Step Response ΔI ΔV Response Time | | 2.0 2 | 50 | %FL Vdc ms | ΔI/Δt slew rate 1A/μs. Settling time to within regulation requirements. |
| Overload Power Limit Current Limit Inception ³ | 2000 102 | | 108 | W %FL | Down to -52Vdc Fold_down current limit. (FL = 38.5A @ 52Vdc) |
| Over-voltage Delayed Immediate Latchoff | | | 60 65 | Vdc Vdc | 200msec delayed shutdown to be implemented. Instantaneous shutdown above this point. |
| Three restart attempts may be implemented within a one minute window prior to a latched shutdown | | | | | |
| Over-temperature Warning Shutdown Auto-recoverable | | 5 20 | | °C °C | Implemented prior to commencement of an OT shutdown Below the maximum rating of the device being protected |
| Temperature hysteresis of approximately 10°C provided between shutdown and restart. | | | | | |

1. Below -5°C, the rise time is approximately 5 minutes to protect the bulk capacitors.

2. Complies with GR947 which calls for a minimum rise time proportional to output load.

3. On start-up, a 20 second fold-down current limit is activated to permit system start-up when units are plugged in one at a time. Beyond 20 seconds, hiccup mode of operation with approximately a 10% duty cycle is enabled. A latched mode current limit can be activated via an I2c command. During hiccup performance the power supply would shut down when the output voltage falls below 39Vdc.



| Auxiliary Output | | | | | |
|-------------------------|-------|-----|------|---------|-----------------|
| Parameter | Min | Typ | Max | Units | Notes |
| Output Voltage Setpoint | | 5 | | Vdc | |
| Output Current | 0.005 | | 0.75 | A | |
| Overall Regulation | -5 | | +10 | % | |
| Ripple and Noise | | 50 | 100 | mVpk-pk | 20MHz bandwidth |
| Over-voltage Clamp | | | 7 | Vdc | |
| Over-current Limit | 110 | | 175 | %FL | |

| Physical | |
|-----------------|---------------|
| Length (in./mm) | 13.85 / 351.8 |
| Width (in./mm) | 4.00 / 101.6 |
| Height (in./mm) | 1.66 / 42.2 |
| Weight (lb/kg) | 4.6 / 2.1 |

Specifications (continued)

| Environmental | | | | | |
|---|---|---------|-----|---------------------|---|
| Parameter | Min | Typ | Max | Units | Notes |
| Ambient Temperature Operating Ambient Derating | -5 ¹ | 1 2 | 55 | °C °C %/°C | Air inlet from sea level to 5,000 feet. Per 1,000 feet above 5,000 feet. Up to 55°C to a maximum of 70°C |
| Storage Temperature | -40 | | 85 | °C | |
| Humidity | 5 | | 95 | % | Relative humidity, non-condensing |
| Shock and Vibration Operational Test Test Levels Drop and Tip Over | | | | | IEC 68-2 IEC 721-3-2 IEC 68-2-31 |
| Earthquake Rating | 4 | | | Zone | Per Telcordia GR-63-CORE, all floors, when installed in CP Shelf. |
| Acoustic Noise | | 45 | dBA | | Noise is proportional to fan speed, load and ambient temperature. |
| Harmonic Emissions | Per EN/IEC61000-3-2 | | | | |
| Radiated Emissions ⁴ | FCC and CISPR22 (EN55022) - Class B ³ | | | | |
| Conducted Emissions - ac | FCC and CISPR22 (EN55022) Class B Telcordia GR-1089-CORE - Class A | | | | |
| Conducted Emissions - dc | Telcordia GR-1089-CORE and CISPR22 (EN55022) - Class A | | | | |
| ESD | Error free per EN/IEC 61000-4-2 Level 3 (6 kV contact discharge, 8 kV air discharge). | | | | |
| Radiated Immunity | Error free per EN/IEC 61000-4-3 Level 3 (10 V/m). | | | | |
| Electrical Fast Transient Burst | Error free per EN/IEC 61000-4-4 Level 3 (2 kV, 5 kHz repetition rate) | | | | |
| Lightning Surge Error Free Damage Free | EN/IEC61000-4-5 Level 4 (4 kV common mode, 2 kV differential mode). ANSI C62.41 Level A3 (6 kV common and differential mode) | | | | |
| Conducted Immunity | Error free per EN/IEC 61000-4-6 Level 3 (10Vrms). | | | | |
| Reliability (calculated) | | 400,000 | | Hours | At ambient of 25°C at full load per Telcordia SR-332, Reliability Prediction for Electronic Equipment, Method I Case III. |
| Isolation Input-Chassis/Signals Input - Output Output - Chassis | 1500 3000 500 | | | Vrms Vrms Vdc | Per EN60950. Consult factory for testing to this requirement Internal Lineage standard |
| Service Life | | 10 | | Years | 25°C ambient, full load excluding fans. |

1. Designed to start at an ambient as low as -40°C, but may not meet operational limits until above -5°C.
2. Power derating shall consider only temperature variations at nominal line (200 – 240Vrms). The unit may derate faster if the input line is below nominal.
3. Class B radiated emissions compliance requires the addition of a ferrite bead to each power line cord at the shelf-end of the cable. See the figure below.



Status and Control

The rectifier provides three means for monitor/control: analog, PMBus compliant I²C, or RS485 for interfacing to Lineage Power controllers or battery plants.

Details of analog controls are provided in this data sheet under Signal Definitions. Lineage Power will provide separate application notes on PMBus protocol for users to interface to the CPL rectifiers. Contact your local Lineage Power representative for details.

Hot Plug


When rapidly extracting and reinserting modules care should be taken to allow for discharging the internal bias supply so that a predictable restart could be achieved. The way to ensure that the circuit sufficiently discharges is to observe the spinning of the fans after an extraction. The unit should not be reinserted until the fans stop spinning.

Control Definitions

All signals are referenced to Logic GRD unless otherwise noted. See the Signal Definitions Table at the end of this document for further description of all the signals.

Input Signals

Margining: Setpoint of the rectifier can be changed via this input pin. Programming can be either a voltage source or a resistance divider. The margining pin is connected to 3.3Vdc via a 10kΩ resistor inside the rectifier. See graphs below.



An open circuit on this pin reverts the voltage level back to the original setting.

Module Present Signal: This signal has dual functionality. It can be used to alert the system when a module is inserted. Has a 500W resistor in series between this signal and Logic GRD. An external pull-up should not raise the voltage on the pin above 0.25Vdc. If raised the pin is raised to 5Vdc the write_protect feature of the EEPROM is enabled.

Protocol Select: Establishes the communications mode of the power supply, between analog/I²C and RS485 modes. For RS485, connect 10kΩ pull-down resistor to 54_OUT(-DC).

Enable: On/Off control when PMBus communications are utilized as configured by the Protocol pin. This pin must be pulled low to turn **ON** the power supply. The power supply will turn **OFF** if either the **Enable** or the **ON/OFF** pin is released. The Enable function does not exist for the RS485 protocol. This signal is referenced to Logic_GRD.

ON/OFF: This is a short pin utilized for hot-plug applications to ensure that the power supply turns **OFF** before the power pins are disengaged. It also ensures that the power supply turns **ON** only after the power pins have been engaged. Must be connected to 54_OUT (-DC).

Output Signals

Alert #: PMBus interrupt signal.

Fault: This signal goes LO for any failure that requires rectifier replacement. Some of these faults may be due to:

- Fan failure
- Over-temperature condition
- Over-temperature shutdown
- Over-voltage shutdown
- Internal Rectifier Fault

Power Capacity: A HI on this pin indicates rectifier configured for 2000W operation; a LO indicates rectifier configured for 1200W operation.

Alarm Table

| Condition | Power Supply LED State | | | | Monitoring Signals (Referenced to Logic_GRD) | | | |
|--|------------------------|----------------|------------------|--------------|---|-----|-----------------|-------------------|
| | AC OK Green | DC OK Green | Service Amber | Fault Red | Fault | OTW | PFW | Module Present |
| OK | 1 | 1 | 0 | 0 | HI | HI | HI | LO |
| Thermal Alarm (5C before shutdown) | 1 | 1 | 1 | 0 | HI | LO | HI | LO |
| Thermal Shutdown | 1 | 0 | 1 | 1 | LO | LO | HI | LO |
| Defective Fan | 1 | 0 | 0 | 1 | LO | HI | HI | LO |
| Blown AC Fuse in Unit | 1 | 0 | 0 | 1 | LO | HI | LO | LO |
| No AC <15mS (single unit) | 0 | 1 | 0 | 0 | HI | HI | LO ³ | LO |
| AC Present but not within limits | Blinks | 0 | 0 | 0 | HI | HI | LO | LO |
| AC not present ¹ | 0 | 0 | 0 | 0 | HI | HI | LO | LO |
| Boost Stage Failure | 1 | 0 | 0 | 1 | LO | HI | LO | LO |
| Over Voltage Latched Shutdown | 1 | 0 | 0 | 1 | LO | HI | LO | LO |
| Over Current | 1 | Blinks | 0 | 0 | HI | HI | LO | LO |
| Non-catastrophic Internal Failure ² | 1 | 1 | 0 | 1 | LO | HI | HI | LO |
| 1 Missing Module | | | | | | | | HI |
| Standby (remote) | 1 | 0 | 0 | 0 | HI | HI | LO | LO |
| Service Request (PMBus mode) | 1 | 1 | Blinks | 0 | HI | HI | HI | LO |
| Communications Fault (RS485 mode) | 1 | 1 | 0 | Blinks | HI | HI | HI | LO |


¹ This signal is correct if the rectifier is back biased from other rectifiers in the shelf .

² Any detectable fault condition that does not result in the power supply shutting down. For example, ORing FET failure, boost section out of regulation, etc.

³ Signal transition from HI to LO is output load dependent

Output Connector

Mating Connector: AMP 1450572-1





| | Signal | | | | | | Output Power | | Input Power | | | | |
|---|--------|----------|----------|-----------|---------|------------|-----------------|-----------------|-------------|----------------|---------------------|------------------|----|
| | 6 | 5 | 4 | 3 | 2 | 1 | P7 | P6 | P5 | P4 | P3 | P2 | P1 |
| A | SCL_0 | MOD_PRES | PFW | LOGIC_GRD | RS_485+ | UNIT_ADDR | 54_OUT (-DC) | 54_OUT (+DC) | Reserved | EARTH (GND) | LINE-2 (Neutral) | LINE-1 (Line) | |
| B | | OTW | Alert#_0 | | RS_485- | 8V_INT | | | | | | | |
| C | SDA_0 | Margin | Enable | Reset | Ishare | Protocol | | | | | | | |
| D | | Fault | 5VA | Power_Cap | ON/OFF | SHELF_ADDR | | | | | | | |

Connector is viewed from the rear positioned inside the power supply.

Signal pins columns 1 and 2 are referenced to 54_OUT (-DC).

Signal pins columns 3 through 6 are referenced to Logic GRD.

 Last-to-make first-to-break pins.

 First-to-make last-to-break longest pin implemented in the mating connector.

Signal Definitions


All hardware alarm signals (Fault, PFW, OTW) are open drain FETs. These signals should be pulled HI to either 3.3V or 5V. Maximum sink current 5mA. An active LO signal (< 0.4Vdc). All signals are referenced to Logic GRD unless otherwise stated. Contact your Lineage Power representative for more details.

| Function | Label | Type | Description |
|----------------------------|--------------------|--------|---|
| Output Enable | Enable | Input | If shorted to LOGIC_GRD, the rectifier output is enabled when using I ² C mode of operation. May also be toggled to reset a latched OFF rectifier. Function not available in RS485 mode. |
| Power Fail Warning | PFW | Output | An open drain FET; normally HI, indicating output power is present. Changes to LO at least 5msec before the output voltage is lost. |
| I ² C Interrupt | Alert#_0 | Output | Interrupt signal via I ² C lines indicating that service is requested from the host controller. This signal pin is pulled up to 3.3V via a 10kΩ resistor and switches to active LO when an interrupt occurs. |
| Rectifier Fault | Fault | Output | Indicates that an internal fault exists. An open drain FET; normally HI, changes to LO. |
| Module Present | MOD_PRES | Output | Short pin, see Status and Control description for further information on this signal. |
| ON/OFF | ON/OFF | Input | Short pin, connects last and breaks first; used to activate and deactivate output during hot-insertion and extraction, respectively. Ref: 54_OUT (-DC) |
| Protocol select | Protocol | Input | See Status and Control description for further information on this signal. Ref: 54_OUT (-DC). |
| Margining | Margin | Input | Allows changing of output voltage through an analog voltage input or via resistor divider. |
| Over-Temperature Warning | OTW | Output | An open drain FET; normally HI, changes to LO approximately 5°C prior to thermal shutdown. |
| Power Capacity | POWER_CAP | Output | Used to indicate rectifier operation mode; HI indicates 2000W operation and LO indicates 1000W operation. |
| Rectifier address | Unit_addr | Input | Voltage level addressing of rectifiers within a single shelf. Ref: 54_OUT (-DC). |
| Shelf Address | Shelf_addr | Input | Voltage level addressing of rectifiers within multiple shelves. Ref: 54_OUT (-DC). |
| Back bias | 8V_INT | - | Diode OR'ed 8Vdc drain; used to back bias microprocessors and DSP of failed rectifier from operating rectifiers. Ref: 54_OUT (-DC). |
| Standby power | 5VA | Output | 5V at 0.75A provided for external use by either adjacent power supplies or the using system. |
| Current Share | Ishare | - | A single wire interface between each of the power unit forces them to share the load current. Ref: 54_OUT (-DC). |
| I ² C Line 0 | SCL_0, SDA_0 | Input | I ² C line 0. |
| RS485 Line | RS_485+ RS_485- | Input | RS485 line. |

Front Panel LEDs

| | Analog Mode | I ² C Mode | RS485 Mode |
|------------------------------|-------------------------------------|---|--|
| <input type="checkbox"/> ~ | ← | ON: Input ok Blinking: Input out of limits | → |
| <input type="checkbox"/> ... | ← | ON: Output ok Blinking: Overload | → |
| <input type="checkbox"/> ✖ | ON: Over-temperature Warning | ON: Over-temperature Warning Blinking: Service | ON: Over-temperature Warning |
| <input type="checkbox"/> ! | ← ON: Fault → | | ON: Fault Blinking: Not communicating |

Dimensions



Ordering Information

| Item | Description | Comcode |
|--------------|----------------------------------|-------------|
| CP2000AC54SD | Auxiliary Output: 5Vdc at 0.75A. | CC109139928 |



World Wide Headquarters
Lineage Power LLC
 3000 Skyline Drive, Mesquite, TX 75149, USA
+1-800-526-7819
 (Outside U.S.A.: +1-972-284-2626)
www.lineagepower.com
e-mail: techsupport1@lineagepower.com

Asia-Pacific Headquarters
 Tel: +65 6416 4283

Europe, Middle-East and Africa Headquarters
 Tel: +49 898 780 672 80

India Headquarters
 Tel: +91 80 2841 1633

Lineage Power reserves the right to make changes to the product(s) or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

© 2008 Lineage Power LLC, (Mesquite, Texas) All International Rights Reserved.
 Revision : GGS_April 2010