



# AC Disconnects



01

01 Fusible and Non-Fusible AC Disconnects

02 Non-Fusible AC Disconnects Plus GFCI

## Fusible and Non-Fusible AC Disconnects


- Compact size
- Easy installation
- Fusible or non-fusible types
- Plastic or metal enclosures
- Puller or non-automatic switch type disconnections
- Fusible—UL869 Service Equipment
- Non-Fusible—UL 1429 Enclosed Pullout switch



02

## Non-Fusible AC Disconnects Plus GFCI

- Two styles: puller or non-automatic
- 15A Duplex GFCI receptacle included
- Disconnect switch positioned above GFCI receptacle allows easier access
- On pullout model, handle stores inside enclosure in OFF position
- Large, easy-to-read ON/OFF markings
- Cover conveniently stores in up position
- Padlock ring for extra security



# AC Disconnects

## Technical Data



### Steel Disconnects N3R Outdoor Enclosure

Type	Volts	Fusing	Amps	HP Rating	Catalog No.	Std. Pkg.
Pullout	240	Fusible	30	3	TF30R	6
			60	10	TF60R	
		Non-Fusible	60	10	TFN60R	
Non-Automatic	240	Non-Fusible	60	10	TNA60R1 <sup>1</sup>	

<sup>1</sup> Device does not have removable closing cap.



### Plastic Disconnects N3R Outdoor Enclosure

Type	Volts	Fusing	Amps	HP Rating	Catalog No.	Std. Pkg.
Pullout	240	Fusible	30	3	TPF30R	6
			60	10	TPF60R	
		Non-Fusible	60	10	TPN60R1 <sup>1</sup>	
			60	10	TPN60R	
Non-Automatic	240	Non-Fusible	60	10	TPNA60R1 <sup>1</sup>	

<sup>1</sup> Device does not have removable closing cap.



### Steel Disconnects N3R Outdoor Enclosure with Ground Fault Receptacle

Type	Volts	Fusing	Amps	HP Rating	Catalog No.	Std. Pkg.
Pullout	240	Non-Fusible	60	10	TFN60RGFR <sup>1</sup>	6
Non-Automatic					TNA60RGFR <sup>1</sup>	

<sup>1</sup> These disconnects include a GFCI outlet.

### Wire Range

Connector	Copper		Aluminum	
	Solid	Strand	Solid	Strand
Line	14-8	14-2	12-8	12-2
Load	14-8	14-2	12-8	12-2
Neutral	-	-	-	-
Equipment Ground	12-8	12-2	12-8	12-2

### Dimensions (inches)

Catalog No.	Height (A)	Width (B)	Depth (C)
TF30R	7.5	5.19	2.5
TF60R	9.25	5.19	2.5
TFN60R	7.5	5.19	2.5
TFN60RGFR	7.13	5.5	5.19
TNA60R1	7.5	5.19	2.5
TNA60RGFR	7.13	5.5	5.19
TPF30R	7	5.75	3.13
TPF60R	7	5.75	3.13
TPN60R	8	5	3
TPN60R1	7.5	5.19	2.5
TPNA60R1	7	5.75	3.13




ABB Inc.  
305 Gregson Drive  
Cary, NC 27511

© Copyright 2019 ABB. All rights reserved  
Information provided is subject to change without notice. Please verify all details with ABB. All values are design or typical values when measured under laboratory conditions, and ABB makes no warranty or guarantee, express or implied, that such performance will be obtained under end-use conditions.  
GE is a registered trademark used under license from General Electric company.