


Temp.
0 25 40 50 60C



Shift index for long-time delay only.



Industrial Solutions

Current Ratings

15, 20, 25, 30, 35, 40, 45 and 50 Amperes

Voltage Ratings

1-pole – 277 Vac (125 Vdc)

2- and 3-pole – 480 Vac (250 Vdc)

Frequency Rating

60 Hertz

Molded Case Circuit Breaker E 100 LINE

Type TED, 15-50 Amperes Enclosure Compensated Long-Time Delay and Instantaneous Time-Current Curves

Curves show enclosure-compensated circuit breaker in open air, 40°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use rating shift index at top of sheet.

GES6113

Adjustments

Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.

by ABB