


Temp. 0 10-50 60C



Shift index for long-time delay only.

MULTIPLES OF CURRENT RATING



Industrial Solutions

Current Ratings

90, 100, 110, 125 and 150 Amperes

Voltage Ratings

2 and 3 pole – 600 Vac (250 Vdc)
3 pole – 500 Vdc

Frequency Rating

60 Hertz

Molded Case Circuit Breaker E 150 LINE

Types TED, THED, 90-150 Amperes
Ambient Compensated
Long Time Delay and Instantaneous
Time Current Curves

Curves show ambient-compensated circuit breaker in open air, 10°C to 50°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use rating shift index at top of sheet.

GES6121

Adjustments

Long Time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.

by ABB