


MULTIPLES OF SENSOR AMPERE RATING



GE Consumer & Industrial -
Electrical Distribution

Sensor Rating (Amperes)

200, 400, 600, 800, 1000, 1200, 1600,
2000, 2500 Amperes

Voltage Rating

600 Vac

Frequency Rating

50/60 Hertz

**Insulated-Case Circuit Breaker
POWER BREAK® with VersaTrip®**

Types TPSS, THSS
Ground Fault Pickup Settings
and Delay Time-current Curves


Curves apply at 50/60 Hertz and
from -20°C to +55°C breaker ambient.

GES-6161

Adjustments

Ground Fault Unit: Pick-up current settings are
0.3X, 0.4X, 0.5X, 0.6X and 0.7X for 200 to 1600A
sensor ratings, and 0.25X, 0.3X, 0.35X, 0.4X and
0.45X for 2000 to 2500A sensor ratings. Time-delay
bands are maximum, intermediate, and minimum.

MULTIPLES OF SENSOR AMPERE RATING



MULTIPLES OF SENSOR AMPERE RATING

<p>GENERAL ELECTRIC</p> <p>Sensor Rating (Amperes) 200, 400, 600, 800, 1000, 1200, 1600, 2000, 2500 amperes</p> <p>Voltage Rating 600 volts a-c</p> <p>Frequency Rating 50/60 Hertz</p>	<p>INSULATED CASE CIRCUIT BREAKER</p> <p>POWER-BREAK™</p> <p>With VersaTrip®</p> <p>Types TPSS, THSS Ground Fault Pickup Settings and Delay Time-current Curves</p> <p><small>(Curves apply at 50/60 Hertz and from -20C to +55C breaker ambient)</small></p>	<p>GES-6161</p> <p>Adjustments</p> <p>Ground Fault Units: Pick-up current settings are 0.3x, 0.4x, 0.5x, 0.6x, and 0.7x for 200 to 1600A sensor ratings, and 0.25x, 0.3x, 0.35x, 0.4x, and 0.45x for 2000 to 2500A sensor ratings. Time-delay bands are maximum, intermediate, and minimum.</p>
--	---	---