


MULTIPLES OF NAMEPLATE CURRENT RATING



GE Consumer & Industrial -  
Electrical Distribution

**Current Ratings**

2000A Frame — 600, 800, 1000,  
1200, 1600 and 2000 Amperes

**Voltage Ratings**

600 Vac, 250 Vdc

**Frequency Ratings**

50/60 Hertz

**Insulated Case Circuit Breaker  
POWER BREAK™ with MagneTrip™**

Types TPMM, THMM  
Long-time Delay and Instantaneous  
Time-current Curves

Curves show circuit breaker in open air, 0°C  
to 50°C ambient, wired with conductors of  
corresponding rating, no prior load.

**GES-6165**


**Adjustments**

Long-time trip: Current setting is continuously  
adjustable 70-100% of nameplate rating. Long-time  
delay varies with current setting as shown above.

Instantaneous trip: Continuous adjustment, factory  
set on HI.

Blocks show trip range at each setting.

MULTIPLES OF NAMEPLATE CURRENT RATING



MULTIPLES OF NAMEPLATE CURRENT RATING



**GE Electrical  
Distribution & Control**

**Current Ratings**  
2000A Frame — 600, 800, 1000  
1200, 1600 and 2000 amperes  
**Voltage Ratings**  
600 volts ac, 250 volts dc  
**Frequency Ratings**  
50/60 Hertz

**INSULATED CASE CIRCUIT BREAKER  
POWER BREAK™  
With MagneTrip™  
Types TPMM, THMM**

**Long-time Delay and Instantaneous  
Time-current Curves**

(Curves show circuit breaker in open air, 0°C to 50°C ambient, wired with conductors of corresponding rating, no prior load.)

**GES-6165**

**Adjustments**

Long-time trip: Current setting is continuously adjustable 70-100% of nameplate rating. Long-time delay varies with current setting as shown above. Instantaneous trip: Continuous adjustment, factory set on HI.

Blocks show trip range at each setting.

**GE Electrical Distribution & Control 41 Woodford Ave. Plainville, CT 06062**