



GE Consumer & Industrial -
Electrical Distribution

Current Ratings

250, 300, 350 and 400 Amperes

Voltage Ratings

240, 480, 600 Vac

Frequency Rating

50/60 Hertz

Molded Case Circuit Breaker

Type TLB4

Ambient Compensated

Long-time Delay and Instantaneous
Time-current Curves

Curves show ambient-compensated circuit breaker in open air, 10°C to 50°C ambient, wired with 75°C rated conductors with ampere rating corresponding to circuit breaker ampere rating. No prior load.

GES-6225B

Adjustments

Long-time delay thermal trip: not adjustable.

Instantaneous magnetic trip: continuously adjustable, factory set on Hi.

Note 1: For ambient above 50°C and below 10°C shift unity index for long-time delay (thermal) portion of curve to desired ambient.