

## 1.1 GENERAL CHARACTERISTICS

### General characteristics - Frame

### Values

### Unit

Model: Conceptpower DPA 300, UL Series



Power, rated:

Apparent 300 kVA

Active 300 kW

Power, range 100 - 1200 kW

UPS type: online, transformer less, modular, decentralized parallel architecture (DPA)

Parallel capability: up to four (4) frames

Battery: not included

Performance classification: VFI-SS-111

### Mechanical

Dimensions (width × height × depth) 53 x 77.75 x 36 (1347 x 1975 x 914) In (mm)

Mass, approximate (300kW system, with three (3) 100kW modules) 1944 (882)  
(Empty cabinet) 1224 (555) Lbs. (kg)

Acoustic noise (acc. to IEC 62040-3)

In normal mode (at ≤25°C) at 100% / 50% Load 75 / 67 dBA

In battery mode (at ≤25°C) at 100% / 50% Load 73 / 66

### Safety

Access: Operator/Restricted Access

Degree of protection against hazards and water ingress: NEMA 1, IP 20

### Electromagnetic compatibility

Emission UPS Cat/Immunity UPS Cat C3 / C3

### Environmental

Storage temperature range -25 - +70 °C

Operative temperature range 0 - +40 °C

Relative humidity range (non-condensing) ≤ 95 %

Maximum altitude without de-rating 1000 m

Heat Dissipation with 100% linear load	Modules	1	3
	W	4500	13500
BTU	15359	46076	

### Additional and usual information

Connection: 4 wires, 3 phase + Ground (PE)

Cable entry: Top. Bottom cable entry available upon request

Accessibility: Front access only

Unit Color: Powder coat, Midnight Black Wrinkle (Rohm & Haas #12-7001)

### Standards

---

Safety	UL 1778 5th edition, CSA C22.2 No. 107.3-14 Third Edition
--------	-----------------------------------------------------------

---

Electromagnetic Compatibility (EMC)	IEC/EN 62040-2
-------------------------------------	----------------

---

---

**General characteristics - Module**

**Values**

**Unit**

---

Model: Conceptpower DPA 300



Power, rated:

---

Apparent	100	kVA
----------	-----	-----

---

Active	100	kW
--------	-----	----

---

UPS type: online, transformer less, modular, decentralized parallel architecture (DPA)

Parallel capability: Up to four (4) frames

Battery: Not included

Performance classification: VFI-SS-111

---

**Mechanical**

Dimensions (width × height × depth):

27.8 x 6.90 x 29.50 (706 x 175 x

active sub-module/passive sub-module 750) In (mm)

---

Mass, approximate:

121 / 119 (55 / 54) Lbs.  
(kg)

---

**Additional and usual information**

Back feed protection: Included

Color: Black (RAL 9005)

---

## 1.2 INPUT CHARACTERISTICS

Input characteristics	UPS frame values	UPS module values	Unit
Power, rated:	300	100	kW
Voltage (steady-state, r.m.s), rated:		3 x 480V	VAC
Tolerance at 480V	-10 / +15 at <100% load -20 / +15 at <80% load, -30 / +15 at <60% load		%
Frequency, rated		60 +/- 5%	Hz
Current (r.m.s), rated (with battery charged and input 480V)	380	127	A
Maximum (with Battery charging and input 480V)	413	138	A
Total Harmonic Distortion (THDi)		< 3.5	%
In-rush current	< 100% of rated current		%
Power factor	0.99 @ 100% load		
Rated Short Circuit Current Rating (Withstand Current)	100	-	kA
AC power distribution system: TN-S, TN-C, TN-C-S, TT			
Note: in static bypass mode or eco-mode TN-C and TN-C-S can cause PE current to rise above 5% of phase currents.			
Phases required		3	
Neutral required		No	
<b>Additional and usual information</b>			
Connection: 4 wires, 3 phase + PE			
Cable entry: top or bottom			
Accessibility: Front access only			
Walk In/Soft Start: yes			
Single input feed is standard. Dual input feed configurable in the field.			

### 1.3 OUTPUT CHARACTERISTICS


Output characteristics	UPS frame values	UPS module values	Unit
Power, rated:	300	100	kW
AC power distribution system: TN-S, TN-C, TN-C-S, TT			
Available phases		3	
Neutral available		No	
Voltage (steady state, r.m.s.), rated:		3 x 480	VAC
Variation in normal mode/battery mode		$\pm 1.5 / \pm 1.5$	%
Total harmonic distortion (THDv), 100% load, normal mode:			
Linear		< 2.0	%
Non-linear (according to IEC 62040-3)		< 4.0	
Total harmonic distortion, 100 % load, battery mode:			
Linear		< 2.0	%
Non-linear (according to IEC 62040-3)		< 4.0	
Voltage unbalance and phase displacement, 100 % load unbalance		0	°
Voltage transient 100% step load:			
Linear		$\pm 4$	%
Non-linear (according to IEC 62040-3)		$\pm 4$	%
Transfer normal mode --> battery mode		0	%
Frequency (steady-state), rated:		60	Hz
Frequency tolerance / variation in normal mode (frq. Synchronized with mains)		$\pm 2 / \pm 4$	%
Frequency tolerance / variation in battery mode (free-running)		$\pm 0.1$	
Max synch phase error (referred to a 360° cycle)		< 2	°
Max slew-rate		1	Hz/s
Nominal current (In), r.m.s. rated:	361	120	A
Overload on inverter		0.002 @ 150% load, 5 @ 125% load, 20 @ 110% load	min
Inverter Output Short Circuit Capability		300% for 100 ms	-
Load power factor, rated		1.0	-
Displacement (permissible lead-lag range)		(all range) 0	%, s
Online double conversion efficiency in normal mode, linear load:			
100% load		96.00	
75% load		96.20	%
50% load		96.00	
25% load		95.40	
Eco-mode efficiency, linear load		$\geq 99$	%
Crest factor (load supported)		3:1	
<b>Static bypass</b>			
Type: automatic, static switch in each module			
Transfer time: inverter → bypass / bypass → inverter / in eco-mode		<1 / <5 / <6	ms
Rated current	364	121	A
Fault clearing capability (bypass mode) for 20 ms	10xIn	10xIn	A
Overload current on bypass mode (< 25°C)		continuously @ 110% load	min

## 1.4 BATTERY CHARACTERISTICS

Battery characteristics	Values	Unit
Technology: VRLA, vented lead-acid, NiCd		
Battery/DC Nominal Input	540V (nom)	
Number of 12 V jars/blocks	45	
Number of 1.2 V NiCd cells (even and odd)	450	
Battery charger - each module has its own decentralized charger		
Max. current charger capability	60	A
Max. power charger capability	30	kW
Floating voltage (VRLA / NiCd)	2.25 / 1.40	VDC
End of discharge voltage (VRLA / NiCd)	1.70 / 1.05	
r.m.s. ripple current (percentage of the battery capacity )	2	%
Temperature compensation: optional		
Battery test: automatic and periodic battery test (selectable)		

1) IMPORTANT NOTE: At output voltage 480VAC, the minimum number of 12V jars/blocks is 45.

### 1.4.1 Graph: AC/AC efficiency with linear load @ cos (phi) 1 \*



\* Tolerance of  $\pm 0.5\%$  applies on all figures