


Temp. 0 10-50 60C

Shift index for long-time delay only.

MULTIPLES OF CIRCUIT BREAKER CURRENT RATING



GE Consumer & Industrial - Electrical Distribution

**Current Ratings**

60, 70 and 80 Amperes

**Voltage Ratings**

2- and 3-pole - 600 Vac

**Frequency Rating**

60 Hertz

**Molded Case Circuit Breaker E 150 LINE**

Types TED, THED, 60-80 Amperes  
Ambient Compensated  
Long-time Delay and Instantaneous  
Time-current Curves

Curves show ambient-compensated circuit breaker in open air, 10°C to 50°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use rating shift index at top of sheet.

**K215-150**

**Adjustments**

Long-time delay thermal trip: not adjustable.  
Instantaneous magnetic trip: not adjustable.  
**NOTE: Limiters can only be applied to AC breakers.**