



GE Consumer & Industrial -
Electrical Distribution

Current Ratings

100, 125, 150, 175, 200 and 225 Amperes

Voltage Ratings

2- and 3-pole - 240 Vac

Frequency Rating

50/60 Hertz

Molded-Case Circuit Breakers

Type TQD

Long-time Delay and Instantaneous
Time-current Curves

Curves show circuit breaker in open air, 10-50°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use rating shift index at top of sheet.

GES-6108C

Adjustments

Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.