


CURRENT IN MULTIPLES OF RATING PLUG AMPERES



GE Consumer & Industrial -  
Electrical Distribution

**Current Ratings**

Frame Amperes	Rating Plug Amperes
30	15, 20

**Voltage Ratings**

2-pole—480 Vac max.  
3-pole—600 Vac max.

**Molded Case Circuit Breakers  
Type SE with Spectra RMS®  
Solid-state Trip**

Long-time Delay and Instantaneous  
with Tracking Short-time Delay  
Time-current Curves

Curves apply at 50 to 400 Hertz  
and from -20°C to 70°C breaker ambient

**K215-165B**

**Adjustments**

Long-time delay; not adjustable.

Instantaneous pick-up settings in multiples of rating plug rating: MIN, 2, 3, 4, 5, 6, MAX

**Note 1:** Operation above 60 Hertz and 50°C play require thermal and interrupting derating of the circuit breaker. Refer to Selection and Application manual.

**Note 2:** Current limiting range, please refer to inset curve.