



**GE Consumer & Industrial -
Electrical Distribution**

Current Ratings

60, 70 and 80 Amperes

Voltage Ratings

1 Pole 240 Vac
2 and 3 pole - 415 Vac

Frequency Ratings

50/60 Hertz

**Molded Case Circuit Breaker
E 100 LINE**

Type TEB
1, 2 and 3 Pole - 60 to 80 Amperes
Long-time Delay and Instantaneous
Time-current Curves

Curves show enclosure-compensated circuit breaker in open air, 40°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use shift index at top of sheet.

K215-97A

Adjustments

Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.