


Midwest Electric Products

Entergy Approved 4, 6, 8 & 12 Circuit Ringless Meter Socket Load Centers

- Removable covers, embossed stand-offs, and ample gutter space for quick installation and wiring
- G90 galvanized steel or aluminum construction for superior corrosion protection
- Durable polyester powder coat finish resists chipping and fading
- Stainless steel latch and hasp
- Lockable meter, raceway, and utility compartments




- Single phase, 120/240V, three wire, up to 22kAIC rated
- NEMA 3R weatherproof enclosure
- Rated as Service Equipment (Panelboard no. 67 and Meter Socket no. 414)
- Service barriers included for factory installed main circuit breakers
- Underground Service Connection
- 60°C/75°C conductor rating



4, 6, 8 & 12 Circuit Ringless Meter Socket Load Centers Energy Approved

Technical Data


| Model Number | Main Ampere Rating | Max. 1" Spaces (Single Phase) | Main Breaker Style Included | Neutral Installed | Enclosure Style | Short Circuit Rating |
|---------------|--------------------|-------------------------------|-----------------------------|-------------------|-----------------|----------------------|
| R101CB2ETG | 100 | 6 | 100A | Yes | G90 Steel | 22kAIC |
| R208CR2AETG | 200 | 8 | 200A | Yes | G90 Steel | 22kAIC |
| R281CB1ETG | 200 | 4 | 200A | Yes | G90 Steel | 22kAIC |
| R256EB118AETG | 200 | 12 | Main Lug | Yes | Aluminum | 10kAIC |
| R256EB1AETG | 200 | 12 | Main Lug | No | G90 Steel | 10kAIC |
| R256EB1NAETG | 200 | 12 | Main Lug | Yes | G90 Steel | 10kAIC |




Mounting Specifications

| Model Number | Dimensions (inches) | | | Weight (lbs.) |
|---------------|---------------------|--------|-------|---------------|
| | Width | Height | Depth | |
| R101CB2ETG | 17 | 26 | 4.7 | 41 |
| R208CR2AETG | | 28 | | 49 |
| R281CB1ETG | | 28 | | 37 |
| R256EB118AETG | | 26 | | 24 |
| R256EB1AETG | | 26 | | 35 |
| R256EB1NAETG | | 26 | | 35 |


Compartment Configurations




R101CB2ETG



R208CR2AETG



R281CB1ETG



R256EB118AETG
R256EB1AETG
R256EB1NAETG

Information provided is subject to change without notice. Please verify all details with Midwest Electric Products. All values are or typical values when measured under laboratory conditions, and Midwest makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

Midwest Electric Products
305 Gregson Drive
Cary, NC 27511
Customer Service: 866-685-0577 • Fax: 804-965-1041
www.midwestelectric.com

© 2019 Midwest Electric Products

MET-024C (12/19)

