



Temp. 0 10-50 60



Shift index for long-time delay only.

MULTIPLES OF CURRENT RATING



Industrial Solutions

Molded Case Circuit Breaker E 150 LINE

GES6119

Current Ratings

15, 20, 25, 30, 35, 40, 45 and 50 Amperes

Types TED & THED, 15-50 Amperes
Ambient Compensated
Long-time Delay and Instantaneous
Time-current Curves

Adjustments

Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.

Voltage Ratings

1 pole – 347 Vac (125 Vdc) (15-30 amps)
2 and 3 pole – 600 Vac (250 Vdc)

Curves show ambient-compensated circuit breaker in open air, 10°C to 50°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use rating shift index at top of sheet.

Frequency Rating

60 Hertz

by **ABB**

GE is a registered trademark used under license from General Electric Company