


Temp.
0 25 40 50 60



Shift index for long-time delay only.

MULTIPLES OF CURRENT RATING



Industrial Solutions

Current Ratings

90 and 100 Amperes

Voltage Ratings

1 pole – 120 Vac (125 Vdc)
2 and 3 pole – 240 Vac (250 Vdc)

Frequency Rating

50/60 Hertz

Molded Case Circuit Breaker E 100 LINE

Type TEB, 90 and 100 Amperes

Enclosure Compensated

Long-time Delay and Instantaneous Time-current Curves

Curves show enclosure-compensated circuit breaker in open air, 40°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use shift index at top of sheet.

GES6124

Adjustments

Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.

by **ABB**

GE is a registered trademark used under license from General Electric Company