

GE Consumer & Industrial -  
Electrical Distribution

**Current Rating**  
2500 Amperes

**Voltage Ratings**  
600 Vac, 250 Vdc

**Frequency Ratings**  
50/60 Hertz

### Insulated-Case Circuit Breaker POWER BREAK™ with MagneTrip™

Types TPMM, THMM  
Long-time Delay and Instantaneous  
Time-current Curves

Curves show circuit breaker in open air, 0°C  
to 50°C ambient, wired with conductors of  
corresponding rating, no prior load.

## GES-6166


#### Adjustments

Long-time trip: Current setting is continuously  
adjustable 70-100% of nameplate rating. Long-time  
delay varies with current setting as shown above.


Instantaneous trip: Continuous adjustment, factory  
set on HI.

Blocks show trip range at each setting.

MULTIPLES OF NAMEPLATE CURRENT RATING



MULTIPLES OF NAMEPLATE CURRENT RATING

 <p><b>GE Electrical Distribution &amp; Control</b></p> <p><b>Current Rating</b> 2500 amperes</p> <p><b>Voltage Ratings</b> 600 volts ac, 250 volts dc</p> <p><b>Frequency Ratings</b> 50/60 Hertz</p>	<p><b>INSULATED CASE CIRCUIT BREAKER POWER BREAK™ With MagneTrip™ Types TPMM, THMM</b></p> <p><b>Long-time Delay and Instantaneous Time-current Curves</b></p> <p>(Curves show circuit breaker in open air, 0°C to 50°C ambient, wired with conductors of corresponding rating, no prior load.)</p>	<p><b>GES-6166</b></p> <p><b>Adjustments</b></p> <p>Long-time trip: Current setting is continuously adjustable 70-100% of nameplate rating. Long-time delay varies with current setting as shown above. Instantaneous trip: Continuous adjustment, factory set on HI. Blocks show trip range at each setting.</p>
--	---	---

GE Electrical Distribution & Control 41 Woodford Ave. Plainville, CT 06062