

GE Consumer & Industrial -
Electrical Distribution

Current Ratings

1600A Frame — 1600 Amperes
1200A Frame — 200, 400, 600, 800, 1000
and 1200 Amperes

Voltage Ratings

600 Vac, 250 Vdc

Frequency Ratings

50/60 Hertz

**Insulated Case Circuit Breaker
POWER BREAK® with MagneTrip™**

Types TPMM, THMM
Long-time Delay and Short-time Delay
Time-current Curves

Curves show circuit breaker in open air, 0°C
to 50°C ambient, wired with conductors of
corresponding rating, no prior load.


GES-6168

Adjustments

Long-time trip: Current setting is continuously
adjustable 70-100% of nameplate rating. Long-time
delay varies with current setting as shown above.

Short-time delay: Adjustable pickup as indicated by
blocks shown for each setting.

MULTIPLES OF NAMEPLATE CURRENT RATING



MULTIPLES OF NAMEPLATE CURRENT RATING



**GE Electrical
Distribution & Control**

Current Ratings
1600A Frame — 1600 amperes
1200A Frame — 200, 400, 600, 800, 1000
and 1200 amperes
Voltage Ratings
600 volts ac, 250 volts dc
Frequency Rating
50/60 Hertz

**INSULATED CASE CIRCUIT BREAKER
POWER BREAK™
With MagneTrip™
Types TPMM, THMM**

**Long-time Delay and Short-time Delay
Time-current Curves**

(Curves show circuit breaker in open air, 0°C to 50°C ambient, wired with conductors of corresponding rating, no prior load.)

GE-6168

Adjustments

Long-time trip: Current setting is continuously adjustable 70-100% of nameplate rating. Long-time delay varies with current setting as shown above. Short-time delay: Adjustable pickup as indicated by blocks shown for each setting.

GE Electrical Distribution & Control 41 Woodford Ave. Plainville, CT 06062