

MAIN SWITCH MODULE

CATALOG NO. TMP3FT4R
 TYPE 3R ENCLOSURE — RAINPROOF — 400AMP.
 120/240V AC 1 PHASE—3 WIRE
 208Y/120V AC 3 PHASE—4 WIRE
 240/120V AC 3 PHASE—4 WIRE

For use with TMP or TMPR meter modules and TMP main lug modules. Continuous load current not to exceed 80% of the rating of fuses employed in other than motor circuits.

REPLACEMENT PARTS

End Cap — Right (Deep)	TMECR
End Cap — Left (Flat)	TMECL
Switch Assembly (Complete)	TMP3FTS4
Front Cover	TMFC2
Drip Hood	TMDH9
Handle	TMPFH1
Hardware Kit	TMPMSK1
Shroud	TMPSH1

SUITABLE FOR USE AS
SERVICE EQUIPMENT

USE COPPER OR
 ALUMINUM WIRE
 USE 75°C WIRE

TORQUE MAIN BUS JOINT BOLTS 300 LB-INS

Suitable only for top feed.
Order rainproof hubs from
table below.

Conduit Size	Cat.No.
1/2	343L647G3
3/4	343L647G4
1	343L647G5
1-1/4	343L647G6
1-1/2	343L647G7
2	343L647G8
2-1/2	343L647G9
3	343L647G10
3-1/2	343L647G11
4	343L647G12

LUG SPECIFICATIONS

Function	Wire Size CU-AL AWG/MCM	Torque, Lb.-Ins.
Line Terminals	(1) 1/0-750 or (2) 1/0-300	550
Neutral Terminal	(1) 1/0-750 or (2) 1/0-300	550
Grounding Terminal	4-300	250

SHORT CIRCUIT CURRENT RATING

This module is U.L. listed for use on circuits delivering not more than 100,000 RMS symmetrical amperes at 240 volts maximum when Class T fuses are installed. The short circuit rating is limited to the lowest marked short circuit rating of the TMP or TMPR meter module or TMP main lug module.

