

MAIN BREAKER MODULE

CATALOG NO. TMP3SB12R SERIES A
TYPE 3R ENCLOSURE—RAINPROOF—1200 AMP MAX.
120/240V AC 1 PHASE—3 WIRE
208Y/120V AC 3 PHASE—4 WIRE
240/120V AC 3 PHASE—4 WIRE

For use with TMP or TMPR meter modules and TMP main lug module.

SUITABLE FOR USE AS SERVICE EQUIPMENT.	USE COPPER OR ALUMINUM WIRE USE 75°C WIRE
--	--

Suitable for top or bottom feed. For top feed order rainproof hubs from table below.	TORQUE MAIN BUS JOINT BOLTS 300 LB.-INS.
---	---

ALTERNATE RATING PLUGS

Conduit Size	Catalog No.	Amp	Catalog Number
1/2	343L647G3	1000	SRPK1200A1000
3/4	343L647G4		
1	343L647G5		
1 1/4	343L647G6		
1 1/2	343L647G7		
2	343L647G8		
2 1/2	343L647G9		
3	343L647G10		
3 1/2	343L647G11		
4	343L647G12		

REPLACEMENT PARTS/ACCESSORIES

End Cap – Right (Deep)	TMECR
End Cap – Left (Flat)	TMECL
Drip Hood	TMDH9
Front Cover	TMFC8
Hardware Kit	TMPMSK1
120 VAC Shunt Trip	SAST1
240 VAC Shunt Trip	SAST2

LUG SPECIFICATIONS

Function	Wire Size CU-AL AWG/MCM	Torque Lb.-In.
Breaker Terminals	REFER TO CIRCUIT (4) 250-500 (2) 4-300	BREAKER MARKING
Neutral Terminal		275
Grounding Terminal		250

SHORT CIRCUIT CURRENT RATING

This circuit breaker main is U.L. listed for use on a circuit delivering not more than 65,000 RMS SYM amperes at 240 VAC max. when a General Electric type SKHA circuit breaker is installed. Replacement breaker shall be General Electric of the same type and interrupting capacity. The short circuit rating is limited to the lowest marked short circuit rating of the TMP or TMPR meter module or TMP main lug module used.

