



MULTIPLES OF CURRENT RATING

TEMP 0 10-50 60°C  
(Note 1)

TEMP 0 10-50 60°C  
(Note 1)



NOT A CURRENT PRODUCT OFFERING

GES-6229A

Note 2 applies

Note 2 applies

MULTIPLES OF CURRENT RATING

**GE**  
**GE Electrical Distribution & Control**  
General Electric Company  
Plainville, CT 06062

**Current Ratings**  
15, 20, 25, 30, 35 and 40 Amperes

**Voltage Ratings**  
240, 480, 600 Volts ac

**Frequency Rating**  
50/60 Hertz

**Current-Limiting Molded Case Circuit Breaker**  
**Type TEL**

**Ambient Compensated**  
**Long-time Delay and Instantaneous**  
**Time-current Curves**

Curves show ambient-compensated circuit breaker in open air, 10-50°C ambient, wired with 60/75°C rated conductors with ampere rating corresponding to circuit breaker ampere rating. No prior load.

**GES-6229A**

**Adjustments**  
Long-time delay thermal trip: not adjustable.  
Instantaneous magnetic trip: not adjustable.  
Note 1: For ambient above 50°C and below 10°C shift unity index for long-time delay (thermal) portion of curve to desired ambient.  
Note 2: Current limiting range, breaker totally clears prior to 0.01 sec. For additional data refer to I<sub>p</sub> and I<sup>2</sup>T curves.