

# MAIN BREAKER MODULE

**CATALOG NO. TMP3SB4R**  
**TYPE 3R ENCLOSURE-RAINPROOF-400 AMP MAX.**  
**120/240V AC 1 PHASE-3 WIRE**  
**208Y/120V AC 3 PHASE-4 WIRE**  
**240/120V AC 3 PHASE-4 WIRE**

For use with TMP or TMPR meter modules and TMP main lug module.

<p style="text-align: center;"><b>SUITABLE FOR USE AS SERVICE EQUIPMENT.</b></p> <p>Suitable for top or bottom feed. For top feed order rainproof hubs from table below.</p>	<p style="text-align: center;"><b>USE COPPER OR ALUMINUM WIRE</b> <b>USE 75C WIRE</b></p> <p style="text-align: center;"><b>TORQUE MAIN BUS JOINT BOLTS</b> <b>300 LB.-INS.</b></p> <p style="text-align: center;"><b>ALTERNATE RATING PLUGS</b></p> <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="width: 50%;">Amp</th> <th style="width: 50%;">Catalog Number</th> </tr> </thead> <tbody> <tr> <td style="text-align: center;">225</td> <td style="text-align: center;">SRPG400A225</td> </tr> <tr> <td style="text-align: center;">250</td> <td style="text-align: center;">SRPG400A250</td> </tr> <tr> <td style="text-align: center;">300</td> <td style="text-align: center;">SRPG400A300</td> </tr> <tr> <td style="text-align: center;">350</td> <td style="text-align: center;">SRPG400A350</td> </tr> </tbody> </table> <p style="text-align: center;"><b>REPLACEMENT PARTS/ACCESSORIES</b></p> <table border="1" style="width: 100%; border-collapse: collapse;"> <tbody> <tr> <td style="width: 70%;">End Cap - Right (Deep)</td> <td style="text-align: center;">TMECR</td> </tr> <tr> <td>End Cap - Left (Flat)</td> <td style="text-align: center;">TMECL</td> </tr> <tr> <td>Drip Hood</td> <td style="text-align: center;">TMDH9</td> </tr> <tr> <td>Front Cover</td> <td style="text-align: center;">TMFC7</td> </tr> <tr> <td>Hardware Kit</td> <td style="text-align: center;">TMPMSK1</td> </tr> <tr> <td>120 VAC Shunt Trip</td> <td style="text-align: center;">SAST1</td> </tr> <tr> <td>240 VAC Shunt Trip</td> <td style="text-align: center;">SAST2</td> </tr> </tbody> </table>	Amp	Catalog Number	225	SRPG400A225	250	SRPG400A250	300	SRPG400A300	350	SRPG400A350	End Cap - Right (Deep)	TMECR	End Cap - Left (Flat)	TMECL	Drip Hood	TMDH9	Front Cover	TMFC7	Hardware Kit	TMPMSK1	120 VAC Shunt Trip	SAST1	240 VAC Shunt Trip	SAST2
Amp	Catalog Number																								
225	SRPG400A225																								
250	SRPG400A250																								
300	SRPG400A300																								
350	SRPG400A350																								
End Cap - Right (Deep)	TMECR																								
End Cap - Left (Flat)	TMECL																								
Drip Hood	TMDH9																								
Front Cover	TMFC7																								
Hardware Kit	TMPMSK1																								
120 VAC Shunt Trip	SAST1																								
240 VAC Shunt Trip	SAST2																								
<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="width: 30%;">Conduit Size</th> <th style="width: 70%;">Catalog No.</th> </tr> </thead> <tbody> <tr> <td style="text-align: center;">1/2</td> <td style="text-align: center;">343L647G3</td> </tr> <tr> <td style="text-align: center;">3/4</td> <td style="text-align: center;">343L647G4</td> </tr> <tr> <td style="text-align: center;">1</td> <td style="text-align: center;">343L647G5</td> </tr> <tr> <td style="text-align: center;">1 1/4</td> <td style="text-align: center;">343L647G6</td> </tr> <tr> <td style="text-align: center;">1 1/2</td> <td style="text-align: center;">343L647G7</td> </tr> <tr> <td style="text-align: center;">2</td> <td style="text-align: center;">343L647G8</td> </tr> <tr> <td style="text-align: center;">2 1/2</td> <td style="text-align: center;">343L647G9</td> </tr> <tr> <td style="text-align: center;">3</td> <td style="text-align: center;">343L647G10</td> </tr> <tr> <td style="text-align: center;">3 1/2</td> <td style="text-align: center;">343L647G11</td> </tr> <tr> <td style="text-align: center;">4</td> <td style="text-align: center;">343L647G12</td> </tr> </tbody> </table>	Conduit Size	Catalog No.	1/2	343L647G3	3/4	343L647G4	1	343L647G5	1 1/4	343L647G6	1 1/2	343L647G7	2	343L647G8	2 1/2	343L647G9	3	343L647G10	3 1/2	343L647G11	4	343L647G12			
Conduit Size	Catalog No.																								
1/2	343L647G3																								
3/4	343L647G4																								
1	343L647G5																								
1 1/4	343L647G6																								
1 1/2	343L647G7																								
2	343L647G8																								
2 1/2	343L647G9																								
3	343L647G10																								
3 1/2	343L647G11																								
4	343L647G12																								

## LUG SPECIFICATIONS

Function	Wire Size CU-AL AWG/MCM	Torque Lb.-In.
Breaker Terminals	<b>REFER TO CIRCUIT BREAKER MARKING</b>	
Neutral Terminal	(2) 2-600	500
Grounding Terminal	(2) 4-300	250

## SHORT CIRCUIT CURRENT RATING

This circuit breaker main is U.L. listed for use on a circuit delivering not more than 42,000 RMS SYM amperes at 240 VAC max. when a General Electric type SGHA circuit breaker is installed. Replacement breaker shall be General Electric of the same type and interrupting capacity. The short circuit rating is limited to the lowest marked short circuit rating of the TMP or TMPR meter module or TMP main lug module used.

