



MULTIPLES OF CURRENT RATING



NOT A CURRENT PRODUCT OFFERING

MULTIPLES OF CURRENT RATING



GE Consumer & Industrial -
Electrical Distribution

Current Ratings

70, 80, 90, 100, 125, 150, 175
and 225 Amperes

Voltage Ratings

240, 480, 600, Volts ac

**Current Limiting Molded Case
Circuit Breaker**

Type TFL

Ambient Compensated
Long-time Delay, and Instantaneous
Time-current Curves

Curves show ambient-compensated circuit breaker in open air, 10°C - 50°C ambient, wired with 75°C rated (100 amperes and below 60/75°C) conductors with ampere rating corresponding to circuit breaker ampere rating. No prior load.

GES-6236

Adjustments

Long-time delay thermal trip: not adjustable.

Instantaneous magnetic trip:
continuously adjustable.

Note 1: For ambient above 50° C and below 10° C shift unity index for long-time delay (thermal) portion of curve to desired ambient.

Note 2: Current limiting range, breaker totally clears prior to 0.01 sec. For additional data refer to I_p and I²T curves.