

MAIN BREAKER MODULE

CATALOG NO. TMP3SB6R
TYPE 3R ENCLOSURE—RAINPROOF—600 AMP MAX.
120/240V AC 1 PHASE—3 WIRE
208Y/120V AC 3 PHASE—4 WIRE
240/120V AC 3 PHASE—4 WIRE

For use with TMP or TMPR meter modules and TMP main lug module.

SUITABLE FOR USE AS
SERVICE EQUIPMENT.

USE COPPER OR ALUMINUM WIRE
USE 75°C WIRE

Suitable for top or bottom feed.
For top feed order rainproof
hubs from table below.

TORQUE MAIN BUS JOINT BOLTS
300 LB.—INS.

ALTERNATE RATING PLUGS

Conduit Size	Catalog No.	Amp	Catalog Number
1/2	343L647G3	400	SRPG600A400
3/4	343L647G4	450	SRPG600A450
1	343L647G5	500	SRPG600A500
1 1/4	343L647G6	REPLACEMENT PARTS/ACCESSORIES End Cap — Right (Deep) TMECR End Cap — Left (Flat) TMECL Drip Hood TMDH9 Front Cover TMFC7 Hardware Kit TMPMSK1 120 VAC Shunt Trip SAST1 240 VAC Shunt Trip SAST2	
1 1/2	343L647G7		
2	343L647G8		
2 1/2	343L647G9		
3	343L647G10		
3 1/2	343L647G11		
4	343L647G12		

LUG SPECIFICATIONS

Function	Wire Size CU—AL AWG/MCM	Torque Lb.—In.
Breaker Terminals	REFER TO CIRCUIT BREAKER MARKING	
Neutral Terminal	(2) 2—600	500
Grounding Terminal	(2) 4—300	250

SHORT CIRCUIT CURRENT RATING

This circuit breaker main is U.L. listed for use on a circuit delivering not more than 42,000 RMS SYM amperes at 240 VAC max. when a General Electric type SGHA circuit breaker is installed. Replacement breaker shall be General Electric of the same type and interrupting capacity. The short circuit rating is limited to the lowest marked short circuit rating of the TMP or TMPR meter module or TMP main lug module used.

GENERAL  ELECTRIC

E11713
PUB 21201

MADE IN U.S.A.

NEW (9/92)