



MULTIPLES OF CURRENT SETTINGS, C



MULTIPLES OF INSTANTANEOUS PICKUP



GES-9867B

GES-9867B

MULTIPLES OF CURRENT SETTINGS, C

MULTIPLES OF INSTANTANEOUS PICKUP



GE Consumer & Industrial - Electrical Distribution

Available Ratings (Amperes)

Type	Breaker		Current Sensor (S)	Rating Plug (X)
	Model	Frame		
MCCB	SG	600	150	60, 80, 100, 125, 150
			400	150, 200, 225, 250, 300, 350, 400
			600	300, 400, 450, 500, 600
	SK	1200	800	300, 400, 500, 600, 700, 800
			1200	600, 700, 800, 1000, 1200

Voltage Rating: 600 Vac, 50 through 60Hertz

Notes:

1. Operation above 60 Hertz requires thermal and interrupting derating of the circuit breaker.
2. Long-time delay band 4 not available on SG frame
3. For current limiting SG breakers in the current limiting range, please refer to inset.

Molded Case Circuit Breakers

Types SG and SK with MicroVersaTrip Plus™ or MicroVersaTrip PM™

Long-time Current Setting and Delay, Short-time Pickup Setting and Delay, and Instantaneous Pickup Setting Time-Current Curves

Curves apply at 50 to 60 Hertz and from -20°C to 55°C breaker ambient

GES-9867B

Programmer Adjustments

**Long-time Function:**  
**Current Settings (C):** 0.50 to 1.0 in increments of 0.05 multiples of rating plug amps (X).  
**Delay Bands:** 1, 2, 3 and 4. (See Note 2)

**Short-time Function**  
**Pickup Settings:** 1.5 to 9.0 in increments of 0.5 multiples of current setting (C).  
**Delay Bands:** 1, 2, 3 and 4. I²t In, I²t Out

**Instantaneous Function**  
**Pickup Settings:** 1.5 to 10.0 in increments of 0.5 multiples of rating plug amps (X).

**S:** Current Sensor in Amps  
**X:** Rating Plug in Amps  
**\*C:** Current Setting in Amps

\* Appears as LTIME pickup on trip unit setup screen