

# MAIN SWITCH MODULE

CATALOG NO. TMPFB6R  
TYPE 3R ENCLOSURE — RAINPROOF — 600 AMP.  
120/240V AC 1 PHASE — 3 WIRE

For use with TMP or TMPR meter modules and TMP main lug modules. Continuous load current not to exceed 80% of the rating of fuses employed in other than motor circuits.

## REPLACEMENT PARTS

End Cap — Right (Deep)	TMECR
End Cap — Left (Flat)	TMECL
Switch Assembly (Complete)	TMPFBS8
Front Cover	TMFC1
Drip Hood	TMDH8
Handle	TMPFH1
Hardware Kit	TMPMSK1
Shroud	TMPSH1

## TORQUE MAIN BUS JOINT BOLTS

300 LB-INS

Suitable only for bottom feed.

SUITABLE FOR USE AS  
SERVICE EQUIPMENT

USE COPPER OR ALUMINUM WIRE  
USE 75°C WIRE

## LUG SPECIFICATIONS

Function	Wire Size		Torque, Lb.-Ins.
	CU-AL	AWG/MCM	
Line Terminals	(2)	2-600	500
Neutral Terminal	(2)	2-600	500
Grounding Terminal		4-300	250

## SHORT CIRCUIT CURRENT RATING

This module is U.L. listed for use on circuits delivering not more than 100,000 RMS symmetrical amperes at 240 volts maximum when Class T fuses are installed. The short circuit rating is limited to the lowest marked short circuit rating of the TMP or TMPR meter module or TMP main lug module.

**GENERAL**  **ELECTRIC**

REV. A  
Pub. 19854

Made in U.S.A.

E5239