

MAIN BREAKER MODULE

CATALOG NO. TMPSB10R SERIES A
TYPE 3R ENCLOSURE—RAINPROOF—1000 AMP MAX.
120/240V AC 1 PHASE—3 WIRE

For use with TMP or TMPR meter modules and TMP main lug module.

Suitable for top or bottom feed.
For top feed order rainproof hubs from table below.

SUITABLE FOR USE AS
SERVICE EQUIPMENT.

USE COPPER OR ALUMINUM WIRE
USE 75°C WIRE

Conduit Size	Catalog No.
1/2	343L647G3
3/4	343L647G4
1	343L647G5
1 1/4	343L647G6
1 1/2	343L647G7
2	343L647G8
2 1/2	343L647G9
3	343L647G10
3 1/2	343L647G11
4	343L647G12

**TORQUE MAIN BUS JOINT BOLTS
300 LB.-INS.**

ALTERNATE RATING PLUGS

Amp	Catalog Number
800	SRPK1200A800

REPLACEMENT PARTS/ACCESSORIES

End Cap – Right (Deep)	TMECR
End Cap – Left (Flat)	TMECL
Drip Hood	TMDH9
Front Cover	TMFC7
Hardware Kit	TMPMSK1
120 VAC Shunt Trip	SAST1
240 VAC Shunt Trip	SAST2

LUG SPECIFICATIONS

Function	Wire Size CU-AL AWG/MCM	Torque Lb.-In.
Breaker Terminals	REFER TO CIRCUIT BREAKER MARKING	
Neutral Terminal	(4) 250-500	275
Grounding Terminal	(2) 4-300	250

SHORT CIRCUIT CURRENT RATING

This circuit breaker main is U.L. listed for use on a circuit delivering not more than 65,000 RMS SYM amperes at 240 VAC max. when a General Electric type SKHA circuit breaker is installed. Replacement breaker shall be General Electric of the same type and interrupting capacity. The short circuit rating is limited to the lowest marked short circuit rating of the TMP or TMPR meter module or TMP main lug module used.

