

MAIN BREAKER MODULE

**CATALOG NO. TMPSB6R
TYPE 3R ENCLOSURE-RAINPROOF-600 AMP MAX.
120/240V AC 1 PHASE-3 WIRE**

For use with TMP or TMPR meter modules and TMP main lug module.

Suitable for top or bottom feed.
For top feed order rainproof hubs from table below.

**SUITABLE FOR USE AS
SERVICE EQUIPMENT.**

**USE COPPER OR ALUMINUM WIRE
USE 75C WIRE**

| Conduit Size | Catalog No. |
|--------------|-------------|
| 1/2 | 343L647G3 |
| 3/4 | 343L647G4 |
| 1 | 343L647G5 |
| 1 1/4 | 343L647G6 |
| 1 1/2 | 343L647G7 |
| 2 | 343L647G8 |
| 2 1/2 | 343L647G9 |
| 3 | 343L647G10 |
| 3 1/2 | 343L647G11 |
| 4 | 343L647G12 |

**TORQUE MAIN BUS JOINT BOLTS
300 LB.-INS.**

ALTERNATE RATING PLUGS

| Amp | Catalog Number |
|-----|----------------|
| 400 | SRPG600A400 |
| 450 | SRPG600A450 |
| 500 | SRPG600A500 |

REPLACEMENT PARTS/ACCESSORIES

| | |
|------------------------|---------|
| End Cap - Right (Deep) | TMECR |
| End Cap - Left (Flat) | TMECL |
| Drip Hood | TMDH9 |
| Front Cover | TMFC7 |
| Hardware Kit | TMPMSK1 |
| 120 VAC SHUNT TRIP | SAST1 |
| 240 VAC SHUNT TRIP | SAST2 |

LUG SPECIFICATIONS

| Function | Wire Size CU-AL AWG/MCM | Torque Lb.-In. |
|--------------------|----------------------------------|----------------|
| Breaker Terminals | REFER TO CIRCUIT BREAKER MARKING | |
| Neutral Terminal | (2) 2-600 | 500 |
| Grounding Terminal | (2) 4-300 | 250 |

SHORT CIRCUIT CURRENT RATING

This circuit breaker main is U.L. listed for use on a circuit delivering not more than 42,000 RMS SYM amperes at 240 VAC max. when a General Electric type SGHA circuit breaker is installed. Replacement breaker shall be General Electric of the same type and interrupting capacity. The short circuit rating is limited to the lowest marked short circuit rating of the TMP or TMPR meter module or TMP main lug module used.

GENERAL  ELECTRIC