



GE Consumer & Industrial -
Electrical Distribution

Current Ratings

125, 150, 175, 200, 225, 250, 300, 350,
400, 500 and 600 Amperes

Voltage Ratings

600 Vac (250 Vdc)

Frequency Rating

Dc or 60 Cycles

**Integrally Fused
Molded Case Circuit Breaker
TRI-BREAK® LINE**

Type TB6 (125-600 Amperes)
Thermal Trip, Magnetic Trip and
Current Limiter Characteristics

Time vs. RMS Current

K215-74E

Adjustments

Long-time delay thermal trip: not adjustable.

Instantaneous magnetic trip: continuously adjustable,
factory set on HI.