


GE Ventilation Bath Fan

BF85 Specifications



RATING

- 70 CFM / 4.0 sones @ 0.10" wg
- 120V, 0.9A, 60 Hz

APPLICATION

- Acceptable for use over tub or shower when installed in a GFCI-protected branch circuit

GRILL

- White polymeric grill secured in place with torsion springs; easily removed if necessary
- Dimensions: 10" x 10"

BLOWER WHEEL

- One-piece polymeric wheel
- 4 1/2" diameter, 1" wide, 10 fins

MOTOR

- Single coil, plug-in, 2 pole
- Lifetime lubrication, thermally protected
- 120V, 60 Hz, 0.9A

FAN HOUSING

- 23 gauge galvanized metal
- Dimensions: 7 3/8" x 7 1/2" x 3 3/4"
- Double metal thickness mounting tabs

DUCT COLLAR

- Plastic collar for 3" duct connection
- Built-in non-metallic damper for quiet operation

UNIT MOUNTING

- Rated for ceilings insulated to R-40
- Designed for ceiling or wall mounting on joists sized down to 2" x 4"
- Maximum drywall thickness: 3/4"
- Rough-in opening: 7 3/4" x 7 3/4"

EFFECTIVE SQ. FT.

- Bathrooms: up to 70 square feet
- Other rooms: up to 85 square feet

SHIPPING

- Box dimensions: 10 3/4" x 10 1/3" x 4 3/4"
- Unit weight: 4 1/2 lbs.
- Cube: 0.29
- Pallet: 96
- UPC: 7 83164 34327 4

STANDARDS

- UL-507 (Electric Fans)
- CSA C22.2 No. 113 (Fans & Ventilators)
- HVI Certified (Standard 916 Air Flow Test & Standard 915 Procedure for Loudness Rating of Residential Fan Products)



HVI PERFORMANCE DATA

	Static pressure (inches of wg)								
	0	0.05	0.1	0.15	0.2	.025	.03	.035	.04
CFM	78	76	74	71	68	65	63	54	46
RPM	2127	2400	2319	2330	2394	2431	2542	2691	2793
Watts	51	51	50	48	48	47	46	46	45



GE Industrial Systems

General Electric Company
41 Woodford Avenue, Plainville, CT 06062
www.GEindustrial.com
© 2003 General Electric Company