


- NOTES:**
1. OPERATOR INTERFACE PANEL.
  2. MAIN INPUT CIRCUIT BREAKER.
  3. 225A SECONDARY MAIN CIRCUIT BREAKER.
  4. (42) POLE DISTRIBUTION PANELBOARD.
  5. CT STRIP FOR BCMS (OPTIONAL).
  6. 1-4 (50-250A) SUBFEEDS.
  7. RECOMMEND A MINIMUM OF 30" IN REAR OR SIDE OF UNIT FOR MAINTENANCE.
  8. MINIMUM OF 18" CLEARANCE FOR DOOR SWING.
  9. RECOMMEND 6" CLEARANCE BETWEEN VENTILATED SIDES AND WALL FOR PROPER COOLING.
  10. BCMS CIRCUIT BOARD (OPTIONAL).



THIS DRAWING CONTAINS  
 CONFIDENTIAL & PROPRIETARY  
 INFORMATION AND SHALL NOT  
 BE DISCLOSED OR COPIED  
 WITHOUT THE EXPRESSED,  
 WRITTEN PERMISSION OF  
 GENERAL ELECTRIC CO.

TITLE GE ZENITH SERIES MDU, CLASSIC DESIGN 50-150kVd, 1 PANELBOARD & SUBFEED CBS W/ BCMS OPTION		REVISION A2	
DWG. NUMBER DWG11007-GE		CHECKED BY KH	
DRAWN BY RAE		DATE 12-31-12	
DATE 10-28-09		GE Critical Power	

