Critical Power from GE





NE100ECO24ATEZ ECO Priority Rectifier



Features and Advantages

- Compact 1RU form factor provides high power density 24 Watts / Cubic inch.
- Efficient Peak efficiency of 95.6 % occurs at less than 50% load matching sweet spots with customer use patterns.
- Flexibly provides 100 Amps of 24 Volt power from both conventional and sustainable sources of energy.
- Starts and runs at any AC voltage from 95 to 275 Vac.


- Operates over a broad temperature range (-40°C through +75°C).
- Fail safe performance hot insertion capabilities allow for rectifier replacement without system shutdown; soft start and inrush current protection prevent nuisance tripping of upstream breakers.
- Extended service life parallel operation with automatic load sharing ensures that units are not unduly stressed.

Uncompromised Advanced Technology to Simplify Your Network

GE Energy's NE100AC24 Eco Priority Singlephase Rectifier is designed to efficiently transform energy from any source* into the 24 Volt DC power needed for wireless cell sites. This means that one single rectifier can be used globally to meet all your 24 Volt powering needs – even if you have off grid sites that use renewable sources to keep refueling and maintenance cost down. The ECO Priority Rectifier prioritizes the renewable source by using Maximum Power Point Tracking to optimally draw from the renewable source, using grid and generator power only as a compliment to the sustainable source.

Efficiency is market leading for diode protected, true hot pluggable, 24 Volt rectifiers.. The NE100AC24 offers a powerful combination of efficiency, network simplicity and reliability.

Efficiency % Typical at 240V_{ac}



Solar Applications*

ECO Priority Rectifiers efficiently and easily transform solar panel output into telecom grade +24 Volt power. They use a straightforward provisioning method where one rectifier is assigned to manage one string of solar panels, and are a good product match with the most popular mono and poly crystalline solar panels on the market today.

A True System Solution

ECO Priority Rectifiers are part of the proven Infinity Power System specifically designed for wireless sites.

- Monitoring / control the built in microprocessor controls and monitors all critical rectifier functions and communicates with the system controller using the built in Galaxy Protocol serial interface.
- Dual Voltage Compatible unique connector pin designation allows the 24 Volt rectifier to be used in a "Universal" power shelf, alongside DC-DC converters supporting loads at 48 Volts dc.
- Plug and Play installation of the rectifier in a shelf connected to a compatible system controller initializes all set up parameters automatically. No adjustments are needed.

*Ac and solar source capability as of Nov. 2012


Electrical Specifications

INPUT VOLTAGE & OUTPUT POWER


Response to AC input voltage	Operates according to figure, turning on at all V_{in} above 90 V_{ac} . Output power 1200W < 140 V_{ac} 2725W > 175 V_{ac} Output power follows linear path between defined points. 300V max excursion voltage					
AC input current	15-12A @ 100-120V _{ac} 15A @ 200-240V _{ac}					
Power Factor	0.98 @ loads over 50%					
THD	< 5% @ loads over 50%					
Holdover	15 milliseconds, with $V_{out final}$ >21 V					
Frequency	45-66Hz or Dc					
Response to DC input voltage	Maximum Power Point Tracking from 100-310V _{dc} with full power above 250V _{dc}					
DC input current	10A max. Photo Voltaic source only. Output power based on source					
Max system DC voltage	155 V _{dc} max PV system voltage to ground is obtained by mid-string, center point, grounding each string and sizing stings according to lowest recorded temperature at site.					

OUTPUT	
V _{out}	+21-29 V_{dc} range Default = 27.25 V_{dc}
lout	44A @ low input line 100A @ high input line
Regulation	± 0.05% w/controller
Ripple	100 mV _{rms} , 250 mV _{p-p}
Efficiency	Approaching 96%
Soft Start	Starts up into fully discharged batteries.


Output Power vs Input Voltage



Constant Power to 24 Volts



Rated Output Current (at V_{in} > 175V_{ac})



Environmental, Compliance & Physical

-40°C to +75°C (Output derates at 2%/°C beginning at 55°C)
Front to back airflow with onboard temperature controlled fans
0 - 95% (non-condensing) for use in a controlled environment
FCC Part 15, EN 55032 (CISPR32), EN 55035, Level A, GR-1089
EN/IEC 61000-4-5 Level 4 (Error free), ANSI C62.41 Category B 100 kHz ring and 1.2/50µs combination waves (6kV damage free)
ANSI/UL60950-1-2014, EN60950-1 2nd ed+A1+A2, CAN/CSA C22.2 No. 60950-1-07 +Am2: 2014, NEBS GR-1089, GR-63-CORE, CE, RoHS6/6
174Watts, or 594 BTU/hr at full load of 2725 Watts
300k Hours @ 25°C per Telcordia SR-332, Method 1, Case 3
1.63x5.23x13.85in (42x133x352mm), 5.05 lbs (2.2 kg), 5.95 lbs (2.7kg)


Power Unit and Power Unit Shelf Connectors

Power Unit PWB

A4	A3	A2	A1	-48V	-48V	RTN	RTN	RTN	RTN	+24V	+24V	+24V	PE/GND (ACEG)	L2/N	L1
B4	B3	B2	B1			(-48 /	(-48 /	(-48 /	(-48 /				(ACEG)		
C4	C3	C2	C1			+24V)	+24V)	+24V)	+24V)						
D4	D3	D2	D1												
				P12	P11	P10	P9	P8	P7	P6	P5	P4	P3	P2	P1
4x Pins	4x Pins	4x Pins	4x Pins	Blade	Blade	Blade MFBL (long)	Blade MFBL (long)	Blade MFBL (long)	Blade MFBL (long)	Blade	Blade	Blade	Blade MFBL (long)	Blade	Blade

OUTLINE DRAWING

Shown looking into the rear of the power unit




Power Unit Connector - AMP Multi-Beam XL (FCI # 51939-234LF or Tyco # 1900948-1)

Signals and Signal Pins

PIN	LENGTH	SIGNAL	DESCRIPTION						
A1	Long	RS-485-	Non-Inverting RS-485 signal line (RS-485 A)						
B1	Long	RS-485+	Inverting RS-485 signal line (RS-485 B)						
C1	Long	Factory Programming	Reserved for Factory Programming - Open Circuit in the system shelf.						
D1	Long	Return	Signal Return for PSIDn, SIDn, & Interlock						
			Power Units Connect Return to NE Common Return internally.						
			Power Units diode isolate the Return signals from each Power Slot.						
A2	Long	PSID0	Power Slot Address 0	 Logic 1 = Open Circuit (~3.3V). Logic 0 = Connection to the Return signal (~0.7V). 					
B2	Long	PSID1	Power Slot Address 1	Left slot (front view) is Power Slot 1 and has address 000B.					
C2	Long	PSID2	Power Slot Address 2	Power Slot ID signals are connected directly to the Return signal at each Power Slot or left open.					
D2	Long	SID3	Shelf Address 3	 Logic 1 = Connection to Return signal (~0.7V). Logic 0 = Open Circuit (~3.3V). Shelf addresses 1 (00001B) through 31 (11111B) are valid. Shelf address (00000B) is invalid. Address 31 (11111B) disables comm. fail LED 					
A3	Long	SID4	Shelf Address 4						
B3	Long	SID5	Shelf Address 5						
C3	Long	SID6	Shelf Address 6	Power Unit Shelf ID signals connect to Shelf Return left open					
D3	Long	SID7	Shelf Address 7						
A4	Short	Interlock	Disables power conversion within a Power Unit when not connected to the Return signal						
			Power Unit Shelves connect Interlock directly to the Return signal at each Power Slot.						
B4	Long	Factory Programming	Reserved for Factory Programming - Open Circuit in the system shelf.						
C4	Long								
D4	Long								

Physical Interface Dimensions





GΕ **Critical Power** 601 Shiloh Road Plano, TX 75074 +1 877 546 3243 www.gecriticalpower.com

*Registered trademark of the General Electric Company. The GE brand, logo, and lumination are trademarks of the General Electric Company. © 2016 General Electric Company. Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.

NE100ECO24ATEZ-FS, Rev. 06/2016