









GE PROPRIETARY AND CONFIDENTIAL INFORMATION  
 This document is the property of General Electric Company (GE) and contains proprietary information of GE. This document is loaned on the express condition that neither it nor the information contained therein shall be disclosed to others without the express written consent of GE Energy, and that the information shall be used by the recipient only as approved expressly by GE Energy. This document shall be returned to GE upon its request. This document may be subject to certain restrictions under U.S. export control laws and regulations.

DRAWING NO. R138MBC033		REV. A		SHEET 1	
REVISIONS		DATE	APPROVED		
REV. A	ECN000259183	Siva.V 12/26/2022	WILLL		



CONNECTOR	COPPER		ALUMINIUM	
	SOLID	STRANDED	SOLID	STRANDED
LINE	-	6-1/0	-	6-1/0
LOAD "A"	14-10	14-10	-	-
NEUTRAL "B" LARGE HOLE	12-8	12-1/0	10-8	10-1/0
NEUTRAL "C" SMALL HOLE	14-8	14-4	12-8	12-4
EQUIP. GRND. "D"	12-8	12-2	12-8	12-2

G = 1/2", 3/4", 1" KO
I = 1", 1-1/4", 1-1/2", KO
J = 3/4", 1", 1-1/4" KO
H = 9/32" KO

	CIRCUIT PROTECTION	NAME	QUANTITY
MAIN (1 & 3)	THQL21100	2P 120/240V 100AMP	1
"E" 5 & 7	THQL2120GFT	GFCI 2P 20A 120V	1
"F" (2 & 4)	THQL1120	1 POLE 120/240V 20AMP	2

APPLIED PRACTICES	SIGNATURES	DATE
UNLESS OTHERWISE SPECIFIED IN DRAWING	MODEL: TEJA	23-12-22
TOLERANCE ON: 1 PL DECIMALS ± .01	DETAIL: RAM	12-01-23
2 PL DECIMALS ± .005	CHECKED: WILLL	12-01-23
3 PL DECIMALS ± .0005	ENGRG:	
ANGLES ± 1.0	MFG:	
FRACTIONS ±	QUALITY:	
FINISH:	ISSUED:	
CRITICAL TO QUALITY CHARACTERISTIC	DRAWING FILE: R138MBC033M01_OD	
	SOLID MODEL: R111MBC010M01	

**Midwest Electric Products**

TITLE: R138MBC033M01 OUTLINE DRAWING/100A 120/240A MAIN 9" 6-20R/20/20 W/MAIN BRK

TEMPORARY POWER SERVICE EQUIPMENT

SIZE: D DRAWING: R138MBC033 REV: A

SCALE: 1:000 SHEET 1 OF 1

Part must conform to SI 900000 Sect. 4, Toxicity Procedure

