

# GENERAL ELECTRIC

## METER MODULE MAIN BREAKER

**1600 AMPS MAX.**  
(SEE CIRCUIT BREAKER RATING)  
**208Y/120 VAC, 3PH-4W**  
**240/120 VAC, 3PH-4W DELTA**  
**120/240 VAC, 1PH-3W**

### TYPE 3R ENCLOSURE - RAINPROOF

SUITABLE FOR USE AS SERVICE EQUIPMENT

### SUITABLE FOR CENTER-FEED APPLICATIONS ONLY \*

\* HORIZONTAL BUS IS RATED 1200 AMPS MAXIMUM. THE LOAD ON THE HORIZONTAL BUS MUST NOT EXCEED THE HORIZONTAL BUS RATING OF THE INDIVIDUAL METER STACKS IN EITHER DIRECTION, WITH THE MAXIMUM LOAD LIMITED TO THE RATING OF THE MAIN CIRCUIT BREAKER.

SUITABLE ONLY FOR BOTTOM FEED.

INSTALLATION AND USE OF THIS EQUIPMENT SHOULD CONFORM TO ALL LOCAL AND NATIONAL CODES AND REGULATIONS.

FOR USE WITH GENERAL ELECTRIC METER SOCKET MODULES OR MAIN TERMINAL BOXES.

TORQUE HORIZONTAL BUS JOINTS TO 25 LB.- FT. (33.90 N-m)

### SHORT CIRCUIT CURRENT RATING

THIS MAIN BREAKER IS SUITABLE FOR USE ON A CIRCUIT CAPABLE OF DELIVERING NOT MORE THAN 100,000 RMS SYMMETRICAL AMPERES AT 240 VOLTS MAXIMUM. THE SHORT CIRCUIT RATING IS LIMITED TO THE LOWEST MARKED SHORT CIRCUIT CURRENT RATING OF THE METER MODULE OR MAIN TERMINAL BOX USED WITH THIS DEVICE. REPLACEMENT BREAKERS SHALL BE OF THE SAME MANUFACTURER AND TYPE AND SHALL HAVE AN INTERRUPTING CAPACITY EQUAL TO OR GREATER THAN THAT OF THE CIRCUIT BREAKER PRESENTLY INSTALLED.

USE 75°C AL-CU CONDUCTORS.  
USE U.L. LISTED CRIMP CONNECTORS.

IF RAINPROOF HUBS ARE REQUIRED, ORDER FROM THE TABLE BELOW:

SIZE:	CAT. NO.
2"	DS200MH
2-1/2"	DS250MH
3"	DS300MH
3-1/2"	DS350MH
4"	DS400MH
5"	DS500MH