

# MAIN BREAKER MODULE

CATALOG NUMBER TMP3SHB4R  
 TYPE 3R ENCLOSURE - RAINPROOF - 400 AMP.  
 120/240V AC 1 PH-3 WIRE  
 208Y/120V AC 3 PHASE-4 WIRE  
 240/120V AC 3 PHASE-4 WIRE

For use with TMP or TMPR meter modules and TMP main lug module.

SUITABLE FOR USE AS SERVICE EQUIPMENT.

USE COPPER OR ALUMINUM WIRE  
 USE 75°C WIRE

Suitable for top or bottom feed. For top feed order rainproof hubs from table below.

TORQUE MAIN BUS JOINT BOLTS  
 (300 LB.-INS.)

### ALTERNATE RATING PLUGS

Amp	Catalog No.
225	SRPG400A225
250	SRPG400A250
300	SRPG400A300
350	SRPG400A350

Conduit Size	Catalog No.
1/2	343L647G3
3/4	343L647G4
1	343L647G5
1-1/4	343L647G6
1-1/2	343L647G7
2	343L647G8
2-1/2	343L647G9
3	343L647G10
3-1/2	343L647G11
4	343L647G12

### REPLACEMENT PARTS / ACCESSORIES

END CAP-RIGHT (DEEP)	TMECR
END CAP-LEFT (FLAT)	TMECL
DRIP HOOD	TMDH9
FRONT COVER	TMFC7
HARDWARE KIT	TMPMSK1
120 VAC Shunt Trip	SAST1
240 VAC Shunt Trip	SAST2

### LUG SPECIFICATIONS

Function	Wire Size CU-AL AWG/MCM	Torque Lb.-In.
Breaker Terminals	REFER TO CIRCUIT BREAKER MARKING	
Neutral Terminal	(2) 2-600	500
Grounding Terminal	(2) 4-300	250

### SHORT CIRCUIT CURRENT RATING

This circuit breaker main is U.L. listed for use on a circuit delivering not more than 100,000 RMS SYM amperes at 240 VAC max. when a General Electric type SGLA circuit breaker is installed. Replacement breaker shall be General Electric of the same type and interrupting capacity. The short circuit rating is limited to the lowest marked short circuit rating of the TMP or TMPR meter module or TMP main lug module used.

**GENERAL  ELECTRIC**

MADE IN U.S.A.